


REM-106BA3T-9E43B-B3M12
Absolute Rotary Encoder - Multiturn
Industrial Line




Technical data

Type	REM-106BA3T-9E43B-B3M12
ID	100046558
Measuring principle	Optical
General data	
Max. rotational speed	6000 rpm
Moment of inertia of the rotor	6 × 10 ⁻⁶ kgm ²
Output type	Absolute multiturn
Resolution singleturn	19 Bit
Resolution multiturn	24 Bit
	Singleturn scalable
Electrical data	
Operating voltage U _B	10...30 VDC
No-load current	≤ 250 mA
Wire break/reverse polarity protection	yes
Communication protocol	PROFINET
Mechanical data	
Flange type	Flange with mounting element
Flange diameter	Ø 58 mm
Shaft Type	Blind hole shaft
Shaft diameter D (mm)	12.7
Shaft material	Stainless steel
Housing material	Aluminium
Electrical connection	Connector, 3 x M12
Axial shaft load	40 N
Radial shaft load	80 N

Features

- Receptacle with torque stop, Ø 58 mm
- Blind hole shaft, Ø 1/2" (12.7 mm)
- Optical measuring principle
- Shaft material: stainless steel
- Protection class IP67 on housing side
- -40...+80 °C
- Max. 6000 rpm
- 10...30 VDC
- Profinet IO, RT and IRT up to 250 µs
- Encoder profile version 4.2
- Media Redundancy Protocol (MRP)
- Link Layer Discovery Protocol (LLDP)
- Simple Network Management Protocol (SNMP)
- Fast Startup (FSU)
- M12 × 3 connector, 4-pin
- Singleturn resolution scalable up to 19 bit, default 13 bit
- Multiturn resolution up to 24 bit, default 12 bit
- Total resolution scalable up to 43 bit, default 25 bit






Wiring diagram



Technical data

Environmental conditions	
Ambient temperature	-40...+80 °C
Vibration resistance (EN 60068-2-6)	10 g (100 m/s²), 55...2000 Hz
Shock resistance (EN 60068-2-27)	250 g (2500 m/s²), 6 ms
Protection class	IP67
Protection class shaft	IP67
MTTF	19 years

Accessories

Dimension drawing	Type	ID	
	RSSD-RSSD-4422-2M	6635150	Cable for Industrial Ethernet, M12 male connector, D-coded, straight to M12 male connector, D-coded, straight, cable length: 2 m, jacket material: PUR, green
	WSSD-WSSD-4422-2M	6635188	Cable for Industrial Ethernet, M12 male connector, D-coded, angled to M12 male connector, D-coded, angled, cable length: 2 m, jacket material: PUR, green
	RSSD-RJ45S-4422-2M	6635170	Cable for Industrial Ethernet, M12 male connector, D-coded, straight to RJ45 male connector, straight, cable length: 2 m, jacket material: PUR, green
	RSSD-RJ45S-4422-7M	6635579	Cable for Industrial Ethernet, M12 male connector, D-coded, straight to RJ45 male connector, straight, cable length: 2 m, jacket material: PUR, green
	RSSD-RJ45S-4422-8M	6635538	Cable for Industrial Ethernet, M12 male connector, D-coded, straight to RJ45 male connector, straight, cable length: 2 m, jacket material: PUR, green

Dimension drawing	Type	ID	
	RKC4.4T-2/TXL	6625503	Connection cable, M12 female connector, straight, 4-pin, cable length: 2 m, jacket material: PUR, black; cULus approval
	WKC4.4T-2/TXL	6625515	Connection cable, M12 female connector, angled, 4-pin, cable length: 2 m, jacket material: PUR, black; cULus approval