


Operator Panel for Connecting to IO-Link Master

4 Buttons with Lamp

OPIL-E4-IO6



Type	OPIL-E4-IO6
ID	100046892

Supply	
Supply voltage	24 VDC
Admissible range	18...30 VDC
Voltage supply connection	M12
Operating current	Max. 150 mA


IO-Link	
Connectivity IO-Link	1 × M12
IO-Link specification	V 1.1
IO-Link port type	Class A
Frame type	Supports all
Transmission rate	COM 2 / 38.4 kbps

Standard/Directive conformity	
Electromagnetic compatibility	Acc. to EN 61131-2:2007

General Information	
Ambient temperature	-40...+70 °C
Storage temperature	-40...+85 °C
Protection class	IP54

- Robust housing
- 1 × illuminated push button, white light-up ring
- 1 × illuminated push button, blue light-up ring
- 1 × illuminated push button, yellow light-up ring
- 1 × illuminated push button, red light-up ring

M12 × 1 IO-Link



I/O allocation to FIL20-8DXP

			Process data
Position 4	Light	Output I/O ₇	Byte.bit offset 0.7
	Button	Input I/O ₆	Byte.bit offset 0.6
Position 3	Light	Output I/O ₅	Byte.bit offset 0.5
	Button	Input I/O ₄	Byte.bit offset 0.4
Position 2	Light	Output I/O ₃	Byte.bit offset 0.3
	Button	Input I/O ₂	Byte.bit offset 0.2
Position 1	Light	Output I/O ₁	Byte.bit offset 0.1
	Button	Input I/O ₀	Byte.bit offset 0.0