


Isolating transducer 1-channel IM12-AI01-1I-1IU-H0/24VDC/K71



The isolating transducers IM12-AI01-1I-1IU-H0/24VDC/K71 transmit analog measured signals galvanically isolated.

The 1-channel device has one input for the operation of HART 2-wire transducers as well as active and passive HART 2-wire transmitters. Connection is via removable screw terminals.

The device is equipped with an input circuit of 4...20 mA and an output circuit of 4...20 mA (either as source or sink) or 1...5 V (source). The input signals are transmitted 1:1 without interference within a range of 3.8...20.5 mA. In addition, digital signals can also be transmitted bidirectionally in accordance with the HART protocol. Wire breaks (< 3.5 mA) and short circuits (> 22 mA) in the transducer circuit are output as current < 3.5 mA or voltage < 0.875 V.

The devices have a green power LED (Pwr). For each input circuit there is a red status LED. A fault in the input circuit causes the red LED to flash according to NE44.

The device complies with the requirements of NE21.

The device is equipped with removable screw terminals.

- Input circuit monitored for wire break and short circuit
- Complete galvanic isolation
- HART transparent
- Removable screw terminals



Dimensions

Type	IM12-AI01-1I-1IU-H0/24VDC/K71
ID	100051436
Nominal voltage	24 VDC
Operating voltage U_s	10...30 VDC
Power consumption	$\leq 3.8 \text{ W}$
Power dissipation, typical	$\leq 1.4 \text{ W}$
Transmitter connection	
Supply voltage	17 V/20 mA typ.
Input current	4...20 mA
Output circuits	
Output current	Source/sink 4...20 mA (sink: 15...28 V)
Output voltage	1...5 V
Load resistance current output	$\leq 0.8 \text{ k}\Omega$
Short-circuit	Output $< 3.5 \text{ mA}$, if in the input circuit a current $> 22 \text{ mA}$ flows
Wire break	Output $< 3.5 \text{ mA}$, if in the input circuit a current $< 3.5 \text{ mA}$ flows
Response characteristic	
Rise time (10...90 %)	$\leq 5 \text{ ms}$
Fall time (90...10 %)	$\leq 5 \text{ ms}$
Measuring accuracy (including linearity, hysteresis and repeatability)	$\leq 0.05 \text{ % of full scale}$
Temperature drift	$\leq 0.002 \text{ % of full scale/K}$
Galvanic isolation	
Test voltage	2.5 kV RMS
Input 1 to output 1	375 V peak value acc. to EN 60079-11
Input 1 to supply	375 V peak value acc. to EN 60079-11
Output 1 to supply	50 V RMS acc. to EN 50178 and EN 61010-1
Displays/Operating elements	
Operational readiness	Green
Error indication	red



Mechanical data		
Protection class	IP20	
Flammability class acc. to UL 94	V-0	
Ambient temperature	-25...+70 °C	
Storage temperature	-40...+80 °C	
Dimensions	120 x 12.5 x 117 mm	
Weight	151 g	
Mounting instructions	DIN rail (NS35)	
Housing material	Plastic, Polycarbonate/ABS	
Electrical connection	Removable screw terminals, 2-pin	
Terminal cross-section	0.2...2.5 mm² (AWG: 24...14)	
Tightening torque	0.5 Nm	
Tightening torque	4.43 LBS-Inch	
Environmental conditions	Operating height	Up to 2000 m above sea level
	Pollution degree	II
	Surge/Overvoltage category	II (EN 61010-1)
	Standards used	
	Voltage resistance and insulation	
		EN 50178
		EN 61010-1
		EN 50155
		GL VI-7-2
	Shock	
		EN 61373 class B
		EN 50155
		GL VI-7-2
		EN 60068-2-6
		EN 60068-2-27
	Temperature	
		EN 60068-2-1 Ad
		EN 50155
		GL VI-7-2
		EN 60068-2-2 Bd
		EN 60068-2-1
	Air humidity	
		EN 60068-2-38
	EMC	
		EN 50155
		NE21
		EN 61326-1
		EN 61326-3-1
		EN 61000-4-2
		EN 61000-4-3
		EN 61000-4-4
		EN 61000-4-5
		EN 61000-4-6
		EN 61000-4-11
		EN 61000-4-29
		EN 55011
		EN 55016
		EN 50121-3-2
		EN 61000-6-2

Accessories

Type code	Ident no.		Dimension drawing
IMX12-SC-2X-4BK	7580940	Screw terminals for IM(X)12 modules; included in delivery: 4 pcs. of 2-pin black terminals	
IMX12-CC-2X-4BK	7580942	Spring terminals for IM(X)12 modules; included in delivery: 4 pcs. black terminals, 2-pin	