





Technical data



	Observe derating/heat dissipation, see manual
Vibration resistance	55 Hz (1 mm)
Shock resistance	30 g (11 ms)
Protection class	IP65
MTTF	126 years Acc. to SN 29500 (Ed. 99) 25 °C, duty cycle 21 %

data communication can take place between the devices.

Accessories

Dimension drawing	Type	ID	
	RKP46PLB-2-RSP46PLB/TXL	100028666	Extension cable, M12 female connector, straight, 4-pin, L-coded; M12 male connector, straight, 4-pin, L-coded; cable length: 2 m, jacket material: PUR, black
	PSU67-1P-1S-2L-24150-IOL-F	100028305	1-phase power supply unit in IP67, 24 VDC, 15-A output current with IO-Link
	PSU67-11-2440/M	6884141	Power supply unit in IP67, 24 VDC, 4 A output current
	RSSD-RSSD-4414-2M	6441405	Cable for Industrial Ethernet, M12 male connector, D-coded, straight to M12 male connector, straight, cable length: 2 m, jacket material: PUR, green

Accessories

Dimension drawing	Type	ID	
	TBEN-LL-8IOLA	100029880	Compact multiprotocol I/O module, IO-Link master 1.1, 8 class A, 8 universal digital PNP channels 2 A
	TBEN-L5-PLC-10	6814018	