

B1N360V-Q20L60-2UP6X3-H1151 Inclinometer – With two Programmable Switching Points



Technical data

Туре	B1N360V-Q20L60-2UP6X3-H1151
ID	1534051
Measuring principle	Acceleration
General data	
Measuring range	0360 °
measuring range z-axis	0360 °
Number of measuring axes	1
Mounting conditions	Vertical
Repeat accuracy	≤ 0.2 % of full scale
Absolute accuracy (at 25 °C)	± 0.5 °
Temperature coefficient typical	0.03°/K
Resolution	≤ 0.14 °
Electrical data	
Operating voltage	1030 VDC
Residual ripple	≤ 10 % U _{ss}
Residual current	≤ 0.1 mA
Isolation test voltage	≤ 0.5 kV
Output current	≤ 500 mA
Response delay	500 ms
Dropout delay	350 ms
Short-circuit protection	yes / Thermal
Wire breakage/Reverse polarity protec- tion	yes / Complete
Output function	5-pin, NO/NC, 2 × PNP
	Surge protection from +Ub to (Ub - 40V)
Current consumption	35 mA

Features

- Rectangular, height 20 mm
- Plastic, PC
 - Indication of operating voltage and switching state
- Two programmable switching outputs
- Switchpoints selectable in a range between 0° and 360°
- DC 4-wire, 10...30 VDC
- M12 x 1 male connector

Wiring diagram





Functional principle

Inclination is determined by a wear-free semiconducting sensor element.



Technical data

Mechanical data	
Design	Rectangular, Q20L60
Dimensions	60 x 30 x 20 mm
Housing material	Plastic, PC
Electrical connection	Connector, M12 × 1
Environmental conditions	
Ambient temperature	-30+70 °C
Vibration resistance	55 Hz (1 mm)
Shock resistance	30 g (11 ms)
Protection class	IP68 IP69K
MTTF	399 years acc. to SN 29500 (Ed. 99) 40 °C
Power-on indication	LED, Green
Switching state	2 × LEDs, Yellow

Mounting instructions

Mounting instructions/Description



The switchpoints are set with the TX1-Q20L60 teach adapter By actuating the toggle switch T1 (OUT 1), a

By actuating the toggle switch 11 (OUT 1), a bridge is formed between GND and pin 5. By actuating the toggle switch T2 (OUT 2), a bridge is formed between UB and pin 5. The switch-on and off points are freely selectable within 360° degrees.

You can teach-in the switching points either clockwise or counter-clockwise.

Before programming the wanted switchon and off points, move the sensor in start position. For details on programming, please see next page. Should you wish to set the switch-off point yourself, the sensor must also be positioned at this point. The sensor must be installed in vertical position.

A further programming method has already a preset range of 180° . Here, only the switch-on point must be set.

Accessories

GUARD-Q20L60



A9684 Protective housing for Q20L60 inclinometers for protecting against mechanical impact; material: Stainless steel



Instructions for use

Switchpoint adjustable as NO contact counter-clockwise or as NC contact clockwise

Press T1 (T2) for 5 s

Power LED flashes

Place the sensor in the wanted start position

Press T1 (T2) for 1 s to set the switch-on point

Power LED and Output 1 (2) LED flash

Place the sensor in the wanted end position Prace T4 (T2) for 2 a to pat the switch off point

Press T1 (T2) for 3 s to set the switch-off point

Power LED and Output 1 (2) LED flash for 3 s then turn steady

Teach process completed, sensor ready for operation.

Switchpoint adjustable as NO contact clockwise or as NC contact counter-clockwise Press T1 (T2) for 5 s

Power LED flashes

Place the sensor in the wanted start position

Press T1 (T2) for 3 s to set the switch-on point

Power LED and Output 1 (2) LED flash fast

Place the sensor in the wanted end position

Press T1 (T2) for 1 s to set the switch-off point

Power LED and Output 1 (2) LED flash for 3 s then turn steady

Teach process completed, sensor ready for operation.

Switchpoint adjustable as NO contact counter-clockwise or as NC contact clockwise (180° default setting)

Press T1 (T2) for 5 s

Power LED flashes

Place the sensor in the wanted start position

Press T1 (T2) for 1 s to set the switch-on point

Power LED and Output 1 (2) LED flash

Press T1 (T2) for 1 s to set the travel path 180 ° and the hysteresis 1 °

Power LED and Output 1 (2) LED flash for 3 s then turn steady

Teach process completed, sensor ready for operation.

Switchpoint adjustable as NO contact clockwise or as NC contact counter-clockwise (180° default setting)

Press T1 (T2) for 5 s

Power LED flashes

Place the sensor in the wanted start position

Press T1 (T2) for 3 s to set the switch-on point

Power LED and Output 1 (2) LED flash fast

Press T1 (T2) for 3 s to set the travel path 180 $^\circ$ and the hysteresis 1 $^\circ$

Power LED and Output 1 (2) LED flash for 3 s then turn steady

Teach process completed, sensor ready for operation.

T1 = Switching output 1; T2 = Switching output 2 Default settings: Hysteresis 1°