


RS-25S10C-9A16B-R3M12

Absolute Rotary Encoder - Single-Turn Industrial Line




Features

- Clamping flange, Ø 58 mm
- Solid shaft, Ø 10 mm × 20 mm
- Optical measuring principle
- Shaft material: stainless steel
- Protection class IP67 on shaft side
- -40...+80 °C
- Max. 3000 rpm
- Profibus
- Removable bus cover with male connector, 3 × M12
- 360° resolved in 16 bit (65536 positions)
- Scalable, default value 13 bit

Technical data

Type	RS-25S10C-9A16B-R3M12
Ident. no.	1544367
Measuring principle	Photoelectric
Max. Rotational Speed	3000 rpm
Moment of inertia of the rotor	3 x10 ⁻⁶ kgm ²
Starting torque	< 0.05 Nm
Measuring range	0...360 °
Ambient temperature	-40...+80 °C
Operating voltage	10...30 VDC
No-load current	≤ 110 mA
Wire breakage/Reverse polarity protection	yes
Communication protocol	PROFIBUS-DP
Output type	absolute singleturn
Resolution single-turn	16 Bit
	scalable
Design	Solid shaft
Flange type	Clamping flange
Flange diameter	Ø 58 mm
Shaft Type	Solid shaft
Shaft diameter D (mm)	10
Shaft length X	20 mm
Shaft material	Stainless steel
Housing material	Die-cast zinc
Electrical connection	Bus connection
	3 x M12
Axial shaft load	80 N

Wiring diagram



Technical data

Radial shaft load	80 N
Vibration resistance (EN 60068-2-6)	100 m/s ² , 55...2000 Hz
Shock resistance (EN 60068-2-27)	2500 m/s ² , 6 ms
Protection class housing	IP67
Protection class shaft	IP67

Signal	BUS-A in	BUS-B in	Shield out	BUS_VDC out	BUS-A out	BUS_GND out	BUS-B out	Shield out	-
Signal -Pin	BUS in 2	BUS in 4	BUS in 5	BUS out 1	BUS out 2	BUS out 3	BUS out 4	BUS out 5	-
Power	U _B	-	0V	-	-	-	-	-	-
Power- Pin	1	2	3	4	5	-	-	-	-

Accessories

RFA-2 **1544631**

Aluminium flange adapter, rectangular, for solid shaft encoders with clamping flange; edge length 63.5 mm; 3 mm thick

RFA-4 **1544633**

Euro flange – aluminium flange adapter for solid shaft encoders, Ø 115 mm; reference diameter 100 mm; adapts 58 mm clamping flange to Euro flange

RFA-6 **1544635**

Aluminium flange adapter for solid shaft encoders with clamping flange, Ø 58 mm; adapts clamping flange to synchro flange

RFA-7 **1544636**

Aluminium flange adapter for solid shaft encoders, Ø 65 mm; adapts to Ø 65 mm flange and 48 mm reference diameter

RFA-8 **1544637**

Aluminium flange adapter for solid shaft encoders with clamping flange, Ø 70 mm; thickness 4 mm, adapts to Ø 70 mm flange

RFA-9 **1544638**


Aluminium angle flange for solid shaft encoders with Ø 58 mm clamping flange

RFA-11 **1544640**


Aluminium flange adapter for solid shaft encoders with clamping flange, Ø 70 mm; thickness 10 mm, adapts to Ø 70 mm flange

RFA-12 **1544641**

Aluminium flange adapter, rectangular, for solid shaft encoders with clamping flange; edge length 70 mm; 10 mm thick

RFA-13
1544642


Aluminium flange adapter, rectangular,
for solid shaft encoders with clamping
flange; edge length 80 mm; 4 mm thick

RFA-1
1544630


Aluminium flange adapter, rectangular,
for solid shaft encoders with clamping
flange; edge length 58 mm; 4 mm thick