

RU200-CK40-2UN8X2T-H1151 Ultrasonic Sensor – Diffuse Mode Sensor



Technical data

Туре	RU200-CK40-2UN8X2T-H1151
ID	1610057
Ultrasonic data	
Function	Proximity switch
Range	502000 mm
Resolution	1 mm
Minimum switching range	20 mm
Ultrasound frequency	120 kHz
Repeat accuracy	\leq 0.25 % of full scale
Edge lengths of the nominal actuator	100 mm
Approach speed	≤ 3 m/s
Pass speed	≤ 3 m/s
Electrical data	
Operating voltage	1530 VDC
Residual ripple	10 % U _{ss}
DC rated operational current	≤ 150 mA
No-load current	≤ 50 mA
Load resistance	≤ 1000 Ω
Residual current	≤ 0.1 mA
Response time typical	< 160 ms
Readiness delay	≤ 300 ms
Output function	NO/NC, NPN
Output 1	Switching output
Output 2	Switching output
Switching frequency	≤3 Hz
Hysteresis	≤ 20 mm
Voltage drop at I _e	≤ 2.5 V



Features

- Separate transducers for transmitter and receiver
- Rectangular housing 40 x 40 mm
- Connection via M12 x 1 male
- Teach range adjustable via button
- Blind zone: 5 cm
- Range: 200 cm
- Resolution: 1 mm
- Aperture angle of sonic cone: ±60 °
- 2 x switching outputs, NPN
- NO/NC programmable

Wiring diagram







Technical data

Short-circuit protection	yes / Latching
Reverse polarity protection	yes
Wire breakage protection	yes
Setting option	Remote Teach
Mechanical data	
Design	Rectangular, CK40
Radiation direction	straight
Dimensions	67 x 40 x 40 mm
Housing material	Plastic, PBT-GF30-V0
Electrical connection	Connector, M12 × 1, 5-wire
Ambient temperature	0+70 °C
Pressure resistance	0.55 bar
Protection class	IP40
Switching state	LED, Yellow
Object detected	LED, Green
Tests/approvals	
Declaration of conformity EN ISO/IEC	EN 60947-5-2
Approvals	CE cULus

Functional principle

Ultrasonic sensors capture a multitude of objects contactlessly and wear-free with ultrasonic waves. It does not matter whether the object is transparent or opaque, metallic or non-metallic, firm, liquid or powdery. Even environmental conditions such as spray, dust or rain hardly affect their function.

The sonic cone diagram indicates the detection range of the sensor. In accordance with standard EN 60947-5-2, quadratic targets in a range of sizes ($20 \times 20 \text{ mm}$, $100 \times 100 \text{ mm}$) and a round rod with a diameter of 27 mm are used.

Important: The detection ranges for other targets may differ from those for standard targets due to the different reflection properties and geometries.

Sonic Cone



Output behaviour



Mounting instructions

Mounting instructions/Description



Setting the limits

The ultrasonic sensor features two switching outputs with teachable switching range. The range is either set via Easy-Teach or via the buttons on the housing. The green and yellow LED indicate whether the sensor has detected an object.

Various functions such as single switchpoint, window mode or reflection mode to a fixed



target can be taught. Further information is described in the operating instructions. How to set the window mode is described below. The limits of the window may be selected freely within the detection range.
Easy-Teach •Connect teach adapter TX1-Q20L60 between sensor and connection cable •For the first limit value, place object accordingly • Press and hold the select button for output 1 or 2 for 2 or 8 s against Gnd • Press and hold the select button for 8 s against Gnd to teach the first limit value. •For the second limit value, place object accordingly •Press and hold button for at least 2 s against Gnd
Teach-Button •For the first limit value, place object accordingly • Press and hold button 1 to select output 1 or 2 for 2 or 8 s against Gnd • Press and hold button 1 for at least 8 s •For the second limit value, place object accordingly • Press and hold button 1 for at least 2 s
After successful teaching, the sensor automatically runs in normal operating mode. Unsuccessful teach-in is signalled by the LED flashing slowly at a frequency of 5Hz.
LED response Successful teaching is indicated by a fast flashing green LED. Thereafter, the sensor automatically runs in normal operating mode. Unsuccessful teaching is indicated by the LED flashing alternately green and yellow. In normal operating mode both LEDs signal the switching state of output 1. •green: object is in the detection range but not in the switching range • vellow: object is in the switching range

yellow: object is in the switching range off: object is outside the switching range

Accessories





Accessories

Dimension drawing



Type TX1-Q20L60 ID 6967114

Teach adapter for inductive encoders, linear position, angle, ultrasonic and capacitive sensors