


RU200-CK40-2UP8X2T-H1151 Ultrasonic Sensor – Diffuse Mode Sensor






Technical data


Туре	RU200-CK40-2UP8X2T-H1151		
ID	1610051		
Ultrasonic data			
Function	Proximity switch		
Range	502000 mm		
Resolution	1 mm		
Minimum switching range	20 mm		
Ultrasound frequency	120 kHz		
Repeat accuracy	≤ 0.25 % of full scale		
Edge lengths of the nominal actuator	100 mm		
Approach speed	≤ 3 m/s		
Pass speed	≤ 3 m/s		
Electrical data			
Operating voltage U _B	1530 VDC		
Residual ripple	10 % U _{ss}		
DC rated operating current I _e	≤ 150 mA		
No-load current	≤ 50 mA		
Load resistance	≤ 1000 Ω		
Residual current	≤ 0.1 mA		
Response time typical	< 160 ms		
Readiness delay	≤ 300 ms		
Output function	NO/NC, PNP		
Output 1	Switching output		
Output 2	Switching output		
Switching frequency	≤3 Hz		
Hysteresis	≤ 20 mm		
Voltage drop at I _e	≤ 2.5 V		

Features

- Separate transducers for transmitter and receiver
- Rectangular housing 40 x 40 mm
- Connection via M12 x 1 male
- Teach range adjustable via button
- ■Blind zone: 5 cm
- Range: 200 cm
- Resolution: 1 mm
- ■Aperture angle of sonic cone: ±60 °
- ■2 x switching outputs, PNP
- ■NO/NC programmable

Wiring diagram







Technical data

Short-circuit protection	yes/Latching		
Reverse polarity protection	yes		
Wire breakage protection	yes		
Setting option	Remote Teach		
Mechanical data			
Design	Rectangular, CK40		
Radiation direction	straight		
Dimensions	67 x 40 x 40 mm		
Housing material	Plastic, PBT-GF30-V0		
Electrical connection	Connector, M12 × 1, 5-wire		
Ambient temperature	0+70 °C		
Pressure resistance	0.55 bar		
Protection class	IP40		
Switching state	LED, Yellow		
Object detected	LED, Green		
Tests/approvals			
Declaration of conformity EN ISO/IEC	EN 60947-5-2		
Vibration resistance	20 g, 1055 Hz, sine, 3 axes, 30 min/axis according to IEC 60068-2-6		
Shock test	30 g, 11 ms, half sine, 3 axes according to IEC 60068-2-27		
Approvals	CE cULus		


Functional principle

Ultrasonic sensors capture a multitude of objects contactlessly and wear-free with ultrasonic waves. It does not matter whether the object is transparent or opaque, metallic or non-metallic, firm, liquid or powdery. Even environmental conditions such as spray, dust or rain hardly affect their function.


The sonic cone diagram indicates the detection range of the sensor. In accordance with standard EN 60947-5-2, quadratic targets in a range of sizes (20×20 mm, 100×100 mm) and a round rod with a diameter of 27 mm are used.

Important: The detection ranges for other targets may differ from those for standard targets due to the different reflection properties and geometries.

Sonic Cone




Output behaviour



Mounting instructions

Mounting instructions/Description



Setting the limits

The ultrasonic sensor features two switching outputs with teachable switching ranges. The range is either set via Easy-Teach or via the buttons on the housing. The green and yellow LEDs indicate whether the sensor has detected the object.

Various functions such as single switchpoint, window mode or reflection mode to a fixed



target can be taught. Further information is described in the operating instructions. How to set the window mode by teaching two limits is described below. These two limits form the switching window and can be selected freely within the detection range.

Easy-Teach

- Connect the teach adapter TX1-Q20L60 between the sensor and connection cable
- · Position object for the first limit value
- Press and hold the button to select output 1 or output 2 against Gnd for min. 2 or min. 8 seconds respectively
- Press and hold the button against Gnd for 8 to 13 seconds to teach the first limit value
- · Position object for the second limit value
- Press and hold button against Gnd for at least 2 seconds

Teach button

- · Position object for the first limit value
- Press button 1 to select output 1 or output 2 for min. 2 or min. 8 seconds respectively
- Press and hold button 1 for 8 to 13 seconds
- · Position object for the second limit value
- Press and hold button 1 for at least 2 seconds

After a successful teach-in, the sensor automatically runs in standard operating mode. Unsuccessful teach-in is signaled by the LED flashing slowly at a frequency of 5 Hz.

LED response

Successful teaching is indicated by a fast flashing green LED. Thereafter, the sensor automatically runs in normal operating mode. Unsuccessful teaching is indicated by the LED flashing alternately green and yellow. In normal operating mode, both LEDs signal the switching state of output 1 of the sensor.

- Green: object within the detection range but not in switching range
- Yellow: object within the switching range
- Off: object outside the detection range

Accessories

Dimension drawing	Type	ID	
M12 x 1 e 15 2 14	RKC4.5T-2/TEL	6625016	Connection cable, M12 female connector, straight, 5-pin, cable length: 2 m, jacket material: PVC, black; cULus approval
0 15 M12 x 1 26.5 32	WKC4.5T-2/TEL	6625028	Connection cable, M12 female connector, angled, 5-pin, cable length: 2 m, jacket material: PVC, black; cULus approval



Accessories

Dimension drawing

Type

ID

TX1-Q20L60

6967114

Teach adapter for inductive encoders, linear position, angle, ultrasonic and capacitive sensors