


# NI50U-CK40-AP6X2-H1141 w/BS4

## Inductive Sensor – With Extended Switching Distance




### Technical data

Type	NI50U-CK40-AP6X2-H1141 w/BS4
ID	1625868
<b>General data</b>	
Rated switching distance	50 mm
Mounting conditions	Non-flush, flush
Secured operating distance	$\leq (0.81 \times S_n)$ mm
Repeat accuracy	$\leq 2 \%$ of full scale
Temperature drift	$\leq \pm 10 \%$ $\leq \pm 20 \%, \leq -25^\circ\text{C} \vee \geq +70^\circ\text{C}$
Hysteresis	3...15 %
<b>Electrical data</b>	
Operating voltage $U_B$	10...30 VDC
Ripple $U_{ss}$	$\leq 10 \%$ $U_{Bmax}$
DC rated operating current $I_o$	$\leq 200$ mA
No-load current	$\leq 15$ mA
Residual current	$\leq 0.1$ mA
Isolation test voltage	0.5 kV
Short-circuit protection	yes/Cyclic
Voltage drop at $I_o$	$\leq 1.8$ V
Wire break/reverse polarity protection	yes/Complete
Output function	3-wire, NO contact, PNP
DC field stability	300 mT
AC field stability	300 mT <sub>ss</sub>
Insulation class	□
Switching frequency	0.25 kHz
<b>Mechanical data</b>	
Design	Rectangular, CK40

### Features

- Rectangular, height 40 mm
- Variable orientation of active face in 5 directions
- Plastic, PBT-GF30-V0
- High luminance corner LEDs
- Optimum view on supply voltage and switching state from any position
- Factor 1 for all metals
- Increased switching distance
- Protection class IP68
- Resistant to magnetic fields
- Auto-compensation protects against pre-damping
- Partially embeddable
- DC 3-wire, 10...30 VDC
- NO contact, PNP output
- M12 x 1 male connector

### Wiring diagram



### Functional principle

Inductive sensors are designed for wear-free and contactless detection of metal objects. uprox+ sensors have significant advantages due to their patented multi-coil system. They excel thanks to their optimum switching


Technical data

distances, maximum flexibility and operational reliability as well as efficient standardization.

Dimensions	65 x 40 x 40 mm
	variable orientation of active face in 5 directions
Housing material	Plastic, PBT-GF20-V0, Black
Active area material	Plastic, PA12-GF30, yellow
Connector housing	metal, CuZn, nickel-plated
Electrical connection	Connector, M12 × 1
Environmental conditions	
Ambient temperature	-30...+85 °C
Vibration resistance	55 Hz (1 mm)
Shock resistance	30 g (11 ms)
Protection class	IP68
MTTF	874 years acc. to SN 29500 (Ed. 99) 40 °C
Power-on indication	2 × LEDs, Green
Switching state	2 × LEDs, Yellow
Included in delivery	Fixing clamp BS4-CK40

Mounting instructions

Mounting instructions/Description



Distance D	240 mm
Distance W	105 mm
Distance S	60 mm
Distance G	300 mm
Distance N	30 mm
Width active area B	40 mm

Flush mounting possible on up to 4 sides  
1-side mounting: Sr = 35 mm; D = 240 mm  
2-side mounting: Sr = 25 mm; D = 240 mm  
3-side mounting: Sr = 20 mm; D = 80 mm  
4-side mounting: Sr = 15 mm; D = 60 mm

Rear-side mounting and set-back installation with reduced switching distance possible

Sensor mounted on metal, set back from the edge:  
x = 10 mm: Sr = 20 mm  
x = 20 mm: Sr = 20 mm  
x = 30 mm: Sr = 20 mm  
x = 40 mm: Sr = 20 mm

Sensor mounted on metal, protruding over the edge:  
y = 10 mm: Sr = 40 mm  
y = 20 mm: Sr = 50 mm  
y = 30 mm: Sr = 50 mm  
y = 40 mm: Sr = 50 mm

Installation in aperture:  
T = 150 mm:  
Sensor with turned rotating bracket  
Surface-mounted on metal Sr = 50 mm  
Surface-mounted on metal, with one side wall Sr = 25 mm  
Surface-mounted on metal, with two side walls Sr = 15 mm  
Surface-mounted on metal, with three side walls Sr = 12 mm

The values stated relate to a 1-mm-thick steel plate.

Sr is the switching distance that can be measured under specified temperature and supply conditions, also taking into account series variation.

## Accessories

BSS-CP40

6901318

Mounting clamp for rectangular housings 40 x 40 mm; material: Polypropylene

