


NI20U-TS12-AP6X2-V1131



Inductive Sensor – Detection of Small and Fast Tube-guided Parts



Features

- Rectangular, height 12 mm
- Plastic, PBT-GF30-V0
- Resistant to magnetic fields
- Factor 1 for all metals
- High sensitivity for detection of small parts
- Output pulse length min. 100 ms
- DC 3-wire, 10...30 VDC
- NO contact, PNP output
- M8 x 1 male connector

Wiring diagram



Functional principle


The highly sensitive sensor detects even small and fast tube-guided parts. Easily mounted with retaining straps. Can be repositioned or replaced during operation. High-quality alternative to simple ring sensors.

Technical data



Type	NI20U-TS12-AP6X2-V1131
ID	1646640
General data	
Rated switching distance	20 mm
Fly-by speed	0...20 m/s
Mounting conditions	Non-flush
Secured operating distance	$\leq (0.81 \times S_n)$ mm
Repeat accuracy	≤ 2 % of full scale
pulse stop	≥ 5 ms
Pulse duration at the output	≥ 100 ms ± 20 %
Temperature drift	$\leq \pm 10$ %
Hysteresis	3...15 %
Electrical data	
Operating voltage U_B	10...30 VDC
Ripple U_{ss}	≤ 10 % U_{Bmax}
DC rated operating current I_o	≤ 200 mA
No-load current	≤ 15 mA
Residual current	≤ 0.1 mA
Isolation test voltage	0.5 kV
Short-circuit protection	yes/Cyclic
Voltage drop at I_o	≤ 1.8 V
Wire break/reverse polarity protection	yes/Complete
Output function	3-wire, NO contact, PNP
DC field stability	300 mT
AC field stability	300 mT _{ss}
Switching frequency	0.008 kHz

Technical data

Mechanical data	
Design	Rectangular, TS12
Dimensions	80 x 17 x 12 mm
Housing material	Plastic, PBT-GF30-V0
Electrical connection	Connector, M8 × 1
Environmental conditions	
Ambient temperature	-25...+70 °C
Vibration resistance	55 Hz (1 mm)
Shock resistance	30 g (11 ms)
Protection class	IP68
MTTF	874 years acc. to SN 29500 (Ed. 99) 40 °C
Power-on indication	LED, Green
Switching state	LED, Yellow
Included in delivery	2 retaining straps



Mounting instructions

Mounting instructions/Description												
												
	<table><tr><td>Distance D</td><td>50 mm</td></tr><tr><td>Distance W</td><td>35 mm</td></tr><tr><td>Distance S</td><td>35 mm</td></tr><tr><td>Distance A</td><td>42 mm</td></tr><tr><td>Distance C</td><td>30 mm</td></tr><tr><td>Width active area B</td><td>17 mm</td></tr></table>	Distance D	50 mm	Distance W	35 mm	Distance S	35 mm	Distance A	42 mm	Distance C	30 mm	Width active area B
Distance D	50 mm											
Distance W	35 mm											
Distance S	35 mm											
Distance A	42 mm											
Distance C	30 mm											
Width active area B	17 mm											
The TS12 has no tailback detection function. To achieve optimal functionality, use only small targets with a max. length of 20 mm.												