


LEDIA70SSD5-XQ

Vision System – Area Light




Technical data

Type	LEDIA70SSD5-XQ
ID	3016234
Signal and display data	
Purpose	Image processing
Function	Area light
Light type	IR
Wavelength	850...940 nm
LED service life (L70)	50000 h
Special features	Wash down
Electrical data	
Operating voltage U_b	24 VDC
DC rated operating current I_o	≤ 350 mA
Max. current consumption per color	500 mA
Mechanical data	
Design	Rectangular
Dimensions	102 x 91 x 28.2 mm
Housing material	Metal, Stainless steel
Window material	Plastic, diffuse
Electrical connection	Connector, M12 × 1, PVC
Number of cores	5
Ambient temperature	0...+50 °C
Protection class	IP68
Tests/approvals	
Approvals	CE, cULus listed

Features

- Sealed stainless steel housing
- Protection class: IP68
- Color: infrared
- Power supply: 24 VDC
- M12 x 1 male
- Plastic window, opaque

Wiring diagram



Functional principle

Area lights are perfectly suited for uniform illumination of a determined area.