


Glass Fiber Bifurcated Fiber BA1.53SMTA



- Operating mode: Diffuse/Retroreflective
- Stainless steel jacket, flexible
- Operating temperature of fiber-optic jacket: -140...+249 °C
- End sleeve for sensor: Stainless steel, narrow angled (90 °)
- Operating temperature of fiber-optic tip: -140...+249 °C:
- Optical fiber, bundle diameter: 2.56 mm
- Optical fiber, total length: ± 914 mm

Functional principle

Glass or plastic fibers are the optimum choice for high-temperature applications and limited spaces. They transfer the light from the sensor to a remote object. Individual fibers are used for opposed mode sensing, whereas bifurcated fibers are suited for retroreflective or diffuse mode operation.

Type	BA1.53SMTA
ID	3020879
Optical data	
Function	Diffuse mode sensor
Fiber-optic type	Glass
Mechanical data	
Housing material	Stainless steel
Jacket material	Stainless-steel mono-winding coil
Jacket material	metal, 1.4310 (AISI 301)
Bundle diameter	2.3 mm
Material of the fiber-optic tip	Stainless Steel
Bending radius	Ø 25 mm
Ambient temperature	-140...+249 °C
Max. temperature tip	249 °C