


Plastic Fiber

Single Conductor — Jacketed Optical Cable Made of Plastic Fiber

PIF46U



- Operation: opposed mode
- 2 pcs. included in delivery
- Polyethylene sheath, flexible
- Operating temperature: -30...+70 °C
- Cable, straight, customizable
- End sleeve for sensor, smooth
- Optical fiber, core diameter 1.0 mm
- Optical fiber, total length: ± 1829 mm

Functional principle

Glass or plastic fibers are the optimum choice for high-temperature applications and limited spaces. They transfer the light from the sensor to a remote object. Individual fibers are used for opposed mode sensing, whereas bifurcated fibers are suited for retroreflective or diffuse mode operation.

Type	PIF46U
ID	3026036

Optical data	
Function	Opposed mode sensor (emitter/receiver)
Fiber-optic type	Plastic

Mechanical data	
Design	Circular
Housing material	Plastic, PE, Black
Jacket material	Polyethylene
Jacket material	plastic, PE
Bundle diameter	1 mm
Material of the fiber-optic tip	Stainless Steel
Bending cycles	10000
Bending radius	Ø 25 mm
Ambient temperature	-30...+70 °C
Max. temperature tip	70 °C