


S18SP6LPQ Photoelectric Sensor – Retroreflective Sensor with Polarizing Filter




Technical data

Туре	S18SP6LPQ
ID	3033450
Optical data	
Function	Retroreflective Sensor
Operating mode	Polarized
Reflector included in delivery	no
Light type	Red polarized
Wavelength	680 nm
Range	502000 mm
Electrical data	
Operating voltage	1030 VDC
No-load current	≤ 30 mA
Short-circuit protection	yes / Cyclic
Reverse polarity protection	yes
Output function	Connection programmable, PNP
Switching frequency	≤ 160 Hz
Readiness delay	≤ 100 ms
Response time typical	< 3 ms
Overcurrent release	> 220 mA
Mechanical data	
Design	Tube, S18
Dimensions	Ø 18 x 78.7 mm
Housing material	Plastic, Thermoplastic material
Lens	plastic, Acrylic
Electrical connection	Connector, M12 × 1, PVC
Number of cores	4

Features

- ■M12 × 1 male connector, 4-pin
- Protection classes IP67/IP69K
- ■Ambient temperature: -40 °C...+70 °C
- Selectable light/dark operation or light operation with alarm function
- Operating voltage: 10...30 VDC
- ■PNP switching output, changeover

Wiring diagram




Functional principle

Retro-reflective sensors incorporate emitter and receiver in a single compact housing. The light beam of the emitter is directed towards a reflector which returns the light back to the receiver. An object is detected when it interrupts this beam. Retro-reflective sensors have a high function gain and good contrast performance. Further it is merely required to install and wire a single device. Excess gain curve Excess gain in relation to the distance

Technical data


Ambient temperature	-40+70 °C
Protection class	IP67 IP69
Special features	Encapsulated Wash down
Power-on indication	LED, Green
Switching state	LED, Yellow
Error indication	LED, green, Flashing
Excess gain indication	LED
Alarm display	LED yellow Flashing
Tests/approvals	
Approvals	CE, UL, CSA




Accessories

ø 18.5 ø 4.6

SMB18A 3033200 Mounting bracket, rectangular, stainless steel, for sensors with 18 mm thread




3012558 Mounting bracket, material VA 1.4401, for M10 x 1.5 thread, thread length 18 mm



Mounting bracket, PTB black, for sensors with 18 mm thread


3053952



3073134 Mounting bracket, stainless steel, for sensors with 18 mm thread

Accessories

Dimension drawing	Туре	ID
	RKC4.4T-2/TEL	6625013



Connection cable, female M12, straight, 4-pin, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com

Accessories

