


Plastic Fiber

Single Conductor — Jacketed Optical Cable Made of Plastic Fiber

PIL46U



- Operation: opposed mode
- 2 pcs. included in delivery
- Polyethylene sheath, flexible
- Operating temperature: -30...+70 °C
- Cable, straight, customizable
- Integrated lens LO8FP
- Optical fiber, core diameter 1.0 mm
- Optical fiber, total length: ± 1829 mm

Functional principle

Glass or plastic fibers are the optimum choice for high-temperature applications and limited spaces. They transfer the light from the sensor to a remote object. Individual fibers are used for opposed mode sensing, whereas bifurcated fibers are suited for retroreflective or diffuse mode operation.

Type	PIL46U
ID	3034080
Optical data	
Function	Opposed mode sensor (emitter/receiver)
Fiber-optic type	Plastic
Mechanical data	
Design	Circular
Housing material	Plastic, PE, Black
Jacket material	Polyethylene
Jacket material	plastic, PE
Bundle diameter	1 mm
Material of the fiber-optic tip	Polyethylene
Bending cycles	10000
Bending radius	Ø 25 mm
Ambient temperature	-30...+70 °C
Max. temperature tip	70 °C