


# Plastic Fiber Bifurcated Fiber PBPM3B36U



- Operation: diffuse/opposed mode
- Polyethylene sheath, flexible
- Operating temperature: -30...+70 °C
- Cable, straight, customizable
- Miniature
- Lateral light emission
- Bendable 2.1 mm

## Functional principle

Glass or plastic fibers are the optimum choice for high-temperature applications and limited spaces. They transfer the light from the sensor to a remote object. Individual fibers are used for opposed mode sensing, whereas bifurcated fibers are suited for retroreflective or diffuse mode operation.

|                                 |                     |
|---------------------------------|---------------------|
| Type                            | PBPM3B36U           |
| ID                              | 3038711             |
| Optical data                    |                     |
| Function                        | Diffuse mode sensor |
| Fiber-optic type                | Plastic             |
| Mechanical data                 |                     |
| Housing material                | Plastic, PE, Black  |
| Jacket material                 | Polyethylene        |
| Jacket material                 | plastic, PE         |
| Material of the fiber-optic tip | Stainless Steel     |
| Bending cycles                  | 10000               |
| Bending radius                  | Ø 20 mm             |
| Ambient temperature             | -30...+70 °C        |