


T18VN6UR W/30

Ultrasonic Sensor – receiver


With Switching Output



Features

- Operating voltage: 10...30 VDC
- Switching output PNP, NO
- Blind zone: 0 cm
- Range: 60 cm

Wiring diagram



Technical data

Type	T18VN6UR W/30
ID	3040095
Ultrasonic data	
Function	Opposed mode sensor
Range	300...600 mm
Ultrasound frequency	230 kHz
Electrical data	
Response time typical	< 1 ms
Readiness delay	≤ 100 ms
Output function	Complementary contact, NPN
Mechanical data	
Design	Rectangular with thread, T18U
Radiation direction	straight
Housing material	Plastic, PBT
Transducer material	Plastic, Epoxyd resin and PU foam
Electrical connection	Cable, 9 m, PVC
Ambient temperature	-40...+70 °C
Protection class	IP67
Tests/approvals	
Approvals	CE


Functional principle

Ultrasonic sensors detect a multitude of objects contactless and wear-free with ultrasonic waves. Regardless of whether the object is transparent or opaque, metallic or non-metallic, liquid, solid or powdery. Even environmental conditions such as spray, dust or rain hardly affect their function.

Accessories


SMB18A 3033200

Mounting bracket, rectangular,
stainless steel, for sensors with 18
mm thread



SMB18AFAM10 3012558

Mounting bracket, material VA
1.4401, for M10 x 1.5 thread, thread
length 18 mm



SMB1815SF 3053279

Mounting bracket, PBT black, for
PICO-GUARD points

