


Q10AP6DQ

Photoelectric Sensor – Diffuse Mode Sensor


Miniature Sensor



Features

- Male connector, M8 × 1, 3-pin
- Protection class IP67
- Glass lens
- Operating voltage: 10...30 VDC
- PNP/NPN switching output, light operation

Wiring diagram




Technical data

Type	Q10AP6DQ
ID	3044862
Optical data	
Function	Proximity switch
Operating mode	Diffuse
Light type	IR
Wavelength	880 nm
Range	1...500 mm
Electrical data	
Operating voltage	10...30 VDC
Residual ripple	< 10 % U _{ss}
DC rated operational current	≤ 150 mA
No-load current	≤ 20 mA
Short-circuit protection	yes / Cyclic
Reverse polarity protection	yes
Output function	NO contact, light operation, PNP
Switching frequency	0.15 kHz
Readiness delay	≤ 100 ms
Response time typical	< 3 ms
Overcurrent release	> 220 mA
Setting option	Potentiometer
Mechanical data	
Design	Rectangular, Q10
Dimensions	42.4 x 20 x 10 mm
Housing material	Plastic, Thermoplastic material, Black
Lens	glass, Glass

Functional principle

Like retroreflective sensors, diffuse mode sensors also contain emitter and receiver circuitry in the same housing. However, diffuse mode sensors do not detect the interruption of the light beam but the reflection of the object. An object is detected if it reflects sufficient light back to the receiver. The switching distance of diffuse mode sensors thus largely depends on the object's reflectivity.

Excess gain curve
Excess gain in relation to distance




Technical data

Electrical connection	Connector, M8 × 1, PVC
Number of cores	3
Ambient temperature	-40...+70 °C
Protection class	IP67
Power-on indication	LED, Green
Switching state	LED, Yellow
Error indication	LED, green, Flashing
Excess gain indication	LED, green
Alarm display	LED yellow Flashing
Tests/approvals	

Accessories

Dimension drawing	Type	ID	
	PKW3Z-2/TEL	6627504	



Connection cable, Ø 8 mm female, angled, 3-pin, snap-on with pull-off protection, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com