

# Q45UR3BA63CQK

## Ultrasonic Sensor – diffuse mode sensor

### With Switching Output

#### Technical data

Type	Q45UR3BA63CQK
ID	3053740
<b>Ultrasonic data</b>	
Function	Proximity switch
Range	50...250 mm
Ultrasound frequency	400 kHz
Repeatability	≤ ± 1 mm
<b>Electrical data</b>	
Response time typical	< 40 ms
Output function	NO contact, PNP
<b>Mechanical data</b>	
Design	Rectangular, Q45
Radiation direction	straight
Dimensions	60.5 x 44.5 x 101.6 mm
Housing material	Plastic, Thermoplastic polyester
Electrical connection	Connector, 7/8", PVC
Ambient temperature	-25...+70 °C
Relative humidity	85 %
Protection class	IP67
<b>Tests/approvals</b>	
Approvals	CE

#### Features

- Switching output, PNP/NPN adjustable
- NO/NC adjustable
- Integrated temperature compensation
- Blind zone: 5 cm
- Range: 25 cm

#### Functional principle


Ultrasonic sensors detect a multitude of objects contactless and wear-free with ultrasonic waves. Regardless of whether the object is transparent or opaque, metallic or non-metallic, liquid, solid or powdery. Even environmental conditions such as spray, dust or rain hardly affect their function.

#### Accessories

SMB30A

3032723

Mounting bracket, rectangular, stainless steel, for sensors with 30mm thread



SMB30MM

3027162

Mounting bracket, rectangular, stainless steel, for sensors with 30 mm thread, wide holes for accurate alignment



SMB30SC

3052521

Mounting bracket, PBT black, for sensors with 30 mm thread, rotatable



## Accessories

Dimension drawing	Type	ID
	MBCC2-506	3061393

## Accessories

Dimension drawing	Type	ID
	M18C2.0	3053022
	Q13C2.0	3059424
	S18C2.0	3056827