


# Q45VR3D Photoelectric Sensor – Diffuse Mode Sensor






Туре	Q45VR3D
ID	3053974
Optical data	
Function	Proximity switch
Operating mode	Diffuse
Light type	IR
Wavelength	880 nm
Range	0450 mm
Electrical data	
Operating voltage	12250 VDC
Operating voltage	24250 VAC
DC rated operational current	≤ 5000 mA
Output function	Complementary contact, Relay output
Switching frequency	0.033 kHz
Switching frequency	≤ 33 Hz
Readiness delay	≤ 100 ms
Response time typical	< 15 ms
Max. DC switching capacity	1 W
Setting option	Potentiometer
Mechanical data	
Design	Rectangular, Q45
Dimensions	Ø 30 x 87.6 x 56.4 x 44.5 mm
Housing material	Plastic, Thermoplastic material
Lens	acrylic, Acrylic
Electrical connection	Cable, 2 m, PVC
Number of cores	5
Core cross-section	0.34 mm <sup>2</sup>



#### **Features**

- ■Cable, PVC, 2 m
- ■Protection class IP67
- Sensitivity adjusted via potentiometer
- Operating voltage: 12...250 VDC or 24... 250 VAC
- ■Relay output, changeover (SPDT)
- Light or dark operation, adjusted via selector switch

#### Wiring diagram



## Functional principle


Like retroreflective sensors, diffuse mode sensors also contain emitter and receiver circuitry in the same housing. However, diffuse mode sensors do not detect the interruption of the light beam but the reflection of the object. An object is detected if it reflects sufficient light back to the receiver. The switching distance of diffuse mode sensors thus largely depends on the object's reflectivity. This type of sensor is especially suited for detection of transparent objects (diffuse mode sensor with or without background suppression or convergent mode sensors).

Excess gain curve Excess gain in relation to distance



### Technical data

Ambient temperature	-40+70 °C
Protection class	IP67
Special features	keep/defer
Power-on indication	LED, Green
Switching state	LED, Yellow
Error indication	LED, green
Excess gain indication	LED, red
Tests/approvals	
MTTF	67 years acc. to SN 29500 (Ed. 99) 40 °C
Approvals	CE, cURus, CSA



### Accessories

© 30,5 6,3 wide Ø 6,3 7,5 R 40 3032723 Mounting bracket, rectangular, stainless steel, for sensors with 30mm thread SMB30FAM10

78.4 60.3

78.4 60.3


75.61,6

48

48

Mounting bracket, stainless steel, for M10 x 1.5 thread, thread length 30 mm  $\,$ 

3011185



Mounting bracket, PBT black, for sensors with 30 mm thread, rotatable

3052521