


QS30DQ

Photoelectric Sensor – Diffuse Mode Sensor





Technical data

Type	QS30DQ
ID	3073095
Optical data	
Function	Proximity switch
Operating mode	Diffuse
Light type	IR
Wavelength	940 nm
Range	2...1000 mm
Electrical data	
Operating voltage	10...30 VDC
Residual ripple	$< 10 \% U_{ss}$
DC rated operational current	$\leq 150 \text{ mA}$
No-load current	$\leq 35 \text{ mA}$
Short-circuit protection	yes
Reverse polarity protection	yes
Output function	NO contact, PNP/NPN
Switching frequency	$\leq 250 \text{ Hz}$
Readiness delay	$\leq 100 \text{ ms}$
Response time typical	$< 2 \text{ ms}$
Setting option	Potentiometer
Mechanical data	
Design	Rectangular with thread, QS30
Dimensions	$\varnothing 30 \times 35 \times 22 \times 57 \text{ mm}$
Housing material	Plastic, Thermoplastic material, Yellow
Lens	plastic, Acrylic
Electrical connection	Connector, M12 x 1, PVC
Number of cores	5

Features

- Male M12 x 1, 5-pin
- Protection class IP67
- LED all-round visible
- Sensitivity adjusted via potentiometer
- Operating voltage: 10...30 VDC
- Switching output, bipolar
- Light or dark operation

Wiring diagram




Functional principle

Identical to retro-reflective sensors, emitter and receiver circuitry are incorporated in the same housing of the diffuse mode sensors. However, diffuse mode sensors do not detect the interruption of the light beam but the reflection of the target. A target is detected if it reflects sufficient light back to the receiver. The switching distance of diffuse mode sensors thus largely depends on the reflectivity of the target.

Excess gain curve
Excess gain in relation to the distance

Technical data

Ambient temperature	-20...+70 °C
Protection class	IP67
Power-on indication	LED, Green
Switching state	LED, Yellow
Error indication	LED, green, Flashing
Excess gain indication	LED, yellow
Tests/approvals	
MTTF	280 years acc. to SN 29500 (Ed. 99) 40 °C
Approvals	CE



Accessories

SMB30A3032723

SMBQS30L3002809

SMB30MM3027162

SMB30SC3052521

Accessories

Dimension drawing	Type	ID	
	WKC4.5T-2/TEL	6625028	Connection cable, female M12, angled, 5-pin, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com

Dimension drawing	Type	ID	
	RKC4.5T-2/TEL	6625016	Connection cable, female M12, straight, 5-pin, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com

