


Plastic Fiber

Single Conductor — Jacketed Optical Cable Made of Plastic Fiber

PIAT46UHFMTA

Type	PIAT46UHFMTA
ID	3073279
Optical data	
Function	Opposed mode sensor (emitter/receiver)
Fiber-optic type	Plastic
Mechanical data	
Design	Circular
Housing material	Plastic, PE, Black
Jacket material	Polyethylene
Jacket material	plastic, PE
Material of the fiber-optic tip	Stainless Steel
Bending cycles	1000
Bending radius	Ø 2 mm
Ambient temperature	-30...+70 °C
Max. temperature tip	70 °C



- Operation: opposed mode
- 2 pcs. included in delivery
- Polyethylene sheath, flexible
- Operating temperature: -30...+70 °C
- DURA-BEND cable, highly flexible, multiple-core, customizable
- End sleeve for probe, angled (90°), threaded

Functional principle

Glass or plastic fibers are the optimum choice for high-temperature applications and limited spaces. They transfer the light from the sensor to a remote object. Individual fibers are used for opposed mode sensing, whereas bifurcated fibers are suited for retroreflective or diffuse mode operation.