


# QS18EP6WQ7

## Photoelectric Sensor – Diffuse Mode Sensor




### Technical data

|                              |                             |
|------------------------------|-----------------------------|
| Type                         | QS18EP6WQ7                  |
| ID                           | 3072009                     |
| <b>Optical data</b>          |                             |
| Function                     | Proximity switch            |
| Operating mode               | Divergent                   |
| Light type                   | IR                          |
| Wavelength                   | 940 nm                      |
| Range                        | 0...300 mm                  |
| <b>Electrical data</b>       |                             |
| Operating voltage            | 10...30 VDC                 |
| DC rated operational current | ≤ 100 mA                    |
| No-load current              | ≤ 35 mA                     |
| Reverse polarity protection  | yes                         |
| Output function              | NO contact, PNP             |
| Switching frequency          | ≤ 833 Hz                    |
| Readiness delay              | ≤ 100 ms                    |
| Response time typical        | < 0.6 ms                    |
| Setting option               | Push Button<br>Remote Teach |
| <b>Mechanical data</b>       |                             |
| Design                       | Rectangular, QS18           |
| Dimensions                   | 21.1 x 15 x 35 mm           |
| Housing material             | Plastic, ABS                |
| Lens                         | plastic, PMMA               |
| Electrical connection        | Connector, M8 × 1, PVC      |
| Number of cores              | 4                           |
| Ambient temperature          | -20...+70 °C                |

### Features

- Male M8 × 1, 4-pin
- Protection class IP67
- LED all-round visible
- Sensitivity adjusted via teach button
- Operating voltage: 10...30 VDC
- PNP switching output
- Light or dark operation

### Wiring diagram



### Functional principle


Identical to retro-reflective sensors, emitter and receiver circuitry are incorporated in the same housing of the diffuse mode sensors. However, diffuse mode sensors do not detect the interruption of the light beam but the reflection of the target. A target is detected if it reflects sufficient light back to the receiver. The switching distance of diffuse mode sensors thus largely depends on the reflectivity of the target. This type of sensor is especially suited for detection of transparent objects (diffuse mode sensor with or without background suppression or convergent mode sensors).

Excess gain curve

## Technical data

|                        |                      |
|------------------------|----------------------|
| Protection class       | IP67                 |
| Special features       | keep/defer           |
| Power-on indication    | LED, Green           |
| Switching state        | LED, Yellow          |
| Error indication       | LED, green, Flashing |
| Excess gain indication | LED                  |
| Alarm display          | LED yellow Flashing  |
| Tests/approvals        |                      |
| Approvals              | CE, cURus            |


Excess gain in relation to the distance



## Accessories

SMB18A


3033200



Mounting bracket, rectangular, stainless steel, for sensors with 18 mm thread

SMBQS18A


3069721



Mounting bracket, stainless steel, for 18 mm thread

SMBQS18AF

3067467



Mounting bracket, stainless steel, for 18 mm thread

## Accessories

| Dimension drawing | Type        | ID      |  |
|-------------------|-------------|---------|--|
|                   | PKG4M-2/TEL | 6625061 |  |



Connection cable, female M8, straight, 4-pin, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see [www.turck.com](http://www.turck.com)

| Dimension drawing | Type        | ID      |  |
|-------------------|-------------|---------|--|
|                   | PKW4M-2/TEL | 6625067 |  |

Connection cable, female M8, angled, 4-pin, cable length: 2 m, sheath material: PVC, black; cULus approval; other cable lengths and qualities available, see [www.turck.com](http://www.turck.com)

