

DS186EQ8

Photoelectric Sensor

Technical data

Type	DS186EQ8
ID	3076526
Optical data	
Function	Opposed mode sensor
Operating mode	Emitter
Wavelength	940 nm
Range	0...20000 mm
Electrical data	
Operating voltage	10...30 VDC
Residual ripple	< 10 % U _{ss}
DC rated operational current	≤ 100 mA
Short-circuit protection	yes
Reverse polarity protection	yes
Readiness delay	≤ 100 ms
Mechanical data	
Design	Rectangular with thread, DS18
Dimensions	Ø 18 x 31.1 x 15 x 59.9 mm
Housing material	Plastic, Thermoplastic material
Lens	Acrylic
Electrical connection	Connector, M12 × 1, PVC
Number of cores	4
Ambient temperature	-20...+70 °C
Protection class	IP67
Excess gain indication	LED
Tests/approvals	



Features

- Operating voltage: 10...30 VDC

Wiring diagram

