


LED Signal Light Beacon K50LMRYA120QP



Type	K50LMRYA120QP
ID	3079191

Signal and display data	
Purpose	LED indicator light
Function	Spotlight
Light type	Red Yellow
LED service life (L70)	50000 h
Dimmable	No
Features of color 1	Magenta, Permanently on
Features of color 2	Red
Features of color 3	Yellow
Special features	Wash down


Electrical data	
Operating voltage U_s	10...30 VDC
DC rated operating current I_s	≤ 40 mA
Max. current consumption per color	15 mA
Input type	AC
Response time typical	< 1 ms

Mechanical data	
Cascadable	No
Design	Dome, K50L
Dimensions	$\varnothing 50 \times 58$ mm
Housing material	Plastic, PC, Black
Window material	Polycarbonate, diffuse
Electrical connection	Cable with connector, 1/2-20UNF-2B, 0.15 m, PVC
Number of cores	5
Ambient temperature	$-40...+50$ °C
Relative humidity	0...90%
Protection class	IP67 IP69


Tests/approvals	
MTTF	249 years acc. to SN 29500 (Ed. 99) 40 °C
Approvals	CE, IECEx

- LED all-round visible
- ATEX category II 2 G, Ex-zone 1
- ATEX category II 1 D, Ex-zone 20
- Individually controllable
- Mechanical screw-in thread M30 x 1.5
- Protection classes IP67/IP69K
- Multicolor: Red (COL 1) / Yellow (COL 2)
- Cable with male end M12 x 1
- Operating voltage 10...30 VDC
- It is envisaged to control always only one color with the appropriate equipment

Wiring Diagram



Accessories

Type code	Ident no.		Dimension drawing
IMX12- DO01-1U-1U-0/24VDC	7580101	Solenoid driver; 1-channel; SIL 2 acc. to IEC 61508; Ex-proof version; monitoring of wire-break and short-circuit; removable screw terminals; 12.5 mm wide; 24 VDC power supply	
IMX12- DO01-2U-2U-0/24VDC	7580105	Solenoid driver; 2-channel; SIL 2 acc. to IEC 61508; Ex-proof version; monitoring of wire-break and short-circuit; removable screw terminals; 12.5 mm wide; 24 VDC power supply	