


WLS28-2MQ


Accessories – Motion switch



Technical data

Type	WLS28-2MQ
ID	3094424
Function	Linear light
Dimmable	No
Operating voltage U_B	12...30 VDC
DC rated operating current I_o	≤ 4000 mA
Cascadable	Yes
Design	Rectangular
Dimensions	79.5 x 28 x 35.9 mm
Housing material	Metal, Anodized AL
Electrical connection	Connector, M12 × 1
Number of cores	4
Ambient temperature	-20...+60 °C
Protection class	IP50


Accessories

Dimension drawing	Type	ID	
	RKC4.4T-2/TEL	6625013	Connection cable, M12 female connector, straight, 4-pin, cable length: 2 m, jacket material: PVC, black; cULus approval

Features


- Inline switch
- M12 male, 4-pin
- M12 female, straight, 4-pin
- Fits WLS28-2 and WLS28-2 dual color versions
- Rugged metal housing in IP50
- For up to 30 VDC and 4 A

Wiring diagram



Functional principle

The energy-efficient LED work lights are ideally suited for industrial applications. The color temperature is between 5,000 and 7,100 Kelvin (cool white). Depending on the model, the luminous flux is 140 or 2600 lumen. Some work lights are switched on/off via supply power (10...30 VDC) and some types by means of a button directly at the LED lamp.

Dimension drawing	Type	ID	
	WKC4.4T-2/TEL	6625025	Connection cable, M12 female connector, angled, 4-pin, cable length: 2 m, jacket material: PVC, black; cULus approval