



LED Signal Light Compact Signal Tower TL50CGYB



- Plastic housing, black
- EMI and RFI immune
- Protection class IP67
- Cable, 2 m
- Multicolor: Green (COL 1) / Yellow (COL 2) / Blue (COL 3)
- Operating voltage: Operating voltage 12...30 VDC or 21...27 VAC with 135 mA per LED color
- Inputs: PNP/NPN

Wiring Diagram



Functional principle

The TL50C compact signal tower is a mixture of the TL50 Beacon and the TL50 high brightness models in a shorter design and ensures highly visible status indicators and a clear user guidance within the entire system. They can be assembled from varicolored LEDs and are available with or without beeper. You can mount them directly on machines, in the cabinet or in monitoring locations of production lines.

The wiring diagram shows a PNP pin assignment.

There are 10 colors available blue (B), green (G), red (R), yellow (Y), white (W), turquoise (T), orange (O), violet (V), sky blue (S) and magenta (M), which specify the light sequence from bottom to top in the type code of the tower light. Example: TL50CGYRQ indicates the colors green, yellow and red from bottom to top

Type	TL50CGYB
ID	3096377
Signal and display data	
Purpose	LED indicator light
Function	Tower light
Light type	Green Yellow Blue
Dimmable	No
Features of color 1	Green, Permanently on, 27 lm
Features of color 2	Yellow, Permanently on, 6 lm
Features of color 3	Blue, Permanently on, 4.5 lm
Electrical data	
Operating voltage U_s	12...30 VDC
DC rated operating current I_s	≤ 135 mA
Operating voltage U_s	21...27VAC
Max. current consumption per color	135 mA
Input type	Bipolar (PNP/NPN)22
Response time typical	< 10 ms
Mechanical data	
Cascadable	No
Design	Smooth barrel, TL50C
Dimensions	Ø 50 x 116.8 mm
Housing material	Plastic, ABS, Black
Window material	Polycarbonate, diffuse
Electrical connection	Cable, 2 m, PVC
Number of cores	4
Ambient temperature	-40...+50 °C
Relative humidity	0...95%
Protection class	IP67
Tests/approvals	
Approvals	CE, UL listed

Accessories

Type code	Ident no.	Dimension drawing
SMB30A	3032723	Mounting bracket, rectangular, stainless steel, for sensors with 30mm thread
SMB30FA	3074005	Montagewinkel; Werkstoff VA 1.4401
SMB30SC	3052521	Mounting bracket, PBT black, for sensors with 30 mm thread, rotatable