



SG-TL70-RGB14

LED Signal Light – Modular Signal Tower

Color Segment



Technical data

Type	SG-TL70-RGB14
ID	3803732
Signal and display data	
Purpose	LED indicator light
Function	Tower light
Light type	RGB
Wavelength	625 nm
Luminous flux lumen	40 lm
LED service life (L70)	50000 h
Dimmable	No
Features of color 1	RGB, Can be set via DIP switches
Electrical data	
Operating voltage U _B	12...30 VDC
Max. current consumption per color	350 mA
Response time typical	< 50 ms
Mechanical data	
Cascadable	No
Design	Smooth barrel, TL70
Dimensions	Ø 70 x 50 mm
Housing material	Plastic, PC, Black
Window material	Polycarbonate, diffuse
Ambient temperature	-40...+50 °C
Relative humidity	0...95 %
Protection class	IP65

Features

- Plastic housing, black
- Protection class IP65 (mounted)
- RGB LEDs
- Switchable between permanent and flashing function
- Operating voltage: 12...30 VDC
- Inputs: PNP/NPN

Functional principle


The rugged multifunction tower lights are available in many variations and are easily mounted. Each tower can be assembled of up to five color segments and, optionally, a beeper. All segments are configurable via DIP switches.

5 colors are available, blue (B), green (G), red (R), yellow (Y) and white (W), which can be used in any combination.





The arrangement of the segments can be modified subsequently and also more segments can be added. Via the basic module the respective port is selected.

Technical data

Tests/approvals	
Approvals	CE, UL listed



Accessories

Dimension drawing	Type	ID	
	B-TL70-5	3092223	TL70 base module, black, cable, 5-pin, 2 m, connection of 4 segments possible
	B-TL70-8	3092224	TL70 base module, black, cable, 8-pin, 2 m, connection of 6 segments possible
	B-TL70-Q5	3092226	TL70 base module, black, connector, 5-pin, M12 x 1, connection of 4 segments possible
	B-TL70-Q8	3092227	TL70 base module, black, connector, 8-pin, M12 x 1, connection of 6 segments possible