


**Actuator/sensor cable, PUR
extension cable
RKC4T-2,5-WSC4T/TXL**



- Female M12, straight, 3-pin
- Male M12, angled, 3-pin
- Sheath material: PUR
- Sheath color: black
- Qualified for drag chain use
- Resistant to weld splatter
- Resistant to chemicals, UV radiation and oils
- Flame retardant
- Free from halogen, silicone, PVC and LABS
- Particularly abrasion resistant
- Approval: cULus
- RoHS conform
- Protection class IP67
- Cable length: 2.5 m

Type code RKC4T-2,5-WSC4T/TXL
Ident no. 6625594


Connector A side
Number of Pins 3
Contacts metal, CuZn, gold-plated
Contact carriers plastic, TPU, black
Grip plastic, TPU, black
Coupling nut/screw metal, CuZn, nickel-plated
Seal plastic, FPM/FKM
Mechanical lifespan > 100 mating cycles
Pollution degree 3
Protection class IP67, A + B side screwed together
Tightening torque 0.8 ... 1 Nm
(observe max. torque of counter piece!)

Connector B side
Number of pins 3
Contacts metal, CuZn, gold-plated
Contact carriers plastic, TPU, black
Grip plastic, TPU, black
Coupling nut/screw metal, CuZn, nickel-plated
Mechanical lifespan > 100 contact durability
Pollution degree 3
Protection class IP67, only in screwed state
Tightening torque 0.8 ... 1 Nm
(observe max. torque of counter piece!)

Cable diameter 4.3mm +/-0.20
Cable length 2.5 m
Cable sheath PUR, black
Core insulation PP
Core colors BN, BU, BK
Core cross-section 3x0.34mm²
Arrangement of strands 42x0.1 mm

Electrical features at +20 °C
Rated Voltage 250 V
Test voltage 2000 V
Ampacity 4 A
Insulation resistance > 30.5 MΩ/km
Forward resistance max. 57 Ω/km

Cable cross-section



Circuit diagram



**Actuator/sensor cable, PUR
extension cable
RKC4T-2,5-WSC4T/TXL**

TURCK

Industrial
Automation

Mechanical and chemical properties

Max. tensile strength (static)	≤ 50 N/mm ²
Max. tensile strength (dynamic)	≤ 20 N/mm ²
Bending radius (stationary laying)	> 5 x Ø
Bending radius (flexible use)	> 10 x Ø
Bending cycles	> 5 mil.
Admissible acceleration	max. 5 m/s ²
Admissible travel path, horizontal	5 m (at 5 m/s ²)
Admissible travel path, vertical	2 m (at 5 m/s ²)
Admissible traversing speed	3.3 m/s
Torsional stress	± 180 °/m
Ambient temperature	
Stationary	-50 ... 80°C
In motion	-25 ... 80°C
Drag chain operation	-25 ... 60°C