



piconet Stand-alone Module for CANopen 8 Digital Outputs 2 A (4 A in Total) SCOB-0008D-0003




- Configuration interface
- Parameterizable functions
- Supported via I/O-ASSISTANT 2
- Direct connection to the fieldbus
- Fibre-glass reinforced housing
- Shock and vibration tested
- Encapsulated module electronics
- Metal connector
- Degree of protection IP67


M12 × 1 Fieldbus



M12 × 1 Output



M8 × 1 Power Supply



$$I_{Bmax} = I_{Lmax} = 4 \text{ A}$$

Type	SCOB-0008D-0003
ID	6824126
Number of channels	8
Operating / load voltage	20...29 VDC
Fieldbus transmission rate	10 kbps ...1 Mbps
Fieldbus addressing	0 to 99
Service interface	parameterisation via I/O-ASSISTANT
Electrical isolation	Fieldbus to operational voltage
Number of channels	8 digital outputs acc. to EN 61131-2
Output voltage	20...29 VDC from load voltage
Output current per channel	2 A (Σ 4 A), short-circuit proof
Load type	resistive, inductive, lamp load
Switching frequency	\leq 500 Hz
Simultaneity factor	0.25
Dimensions (W x L x H)	30 x 175 x 26.5 mm
Vibration test	Acc. to EN 60068-2-6
Shock test	acc. to DIN EN 60068-2-27
Electromagnetic compatibility	Acc. to EN 61000-6-2/EN 61000-6-4
Protection class	IP67
Approvals	CE, cULus