


piconet Stand-alone Module for CANopen


4 Analog Outputs 0...20 mA

SCOB-04A-0009




- 4 analog outputs 0(4)...20 mA
- Configuration interface
- Parameterizable functions
- Supported via I/O-ASSISTANT 2
- Direct connection to the fieldbus
- Fibre-glass reinforced housing
- Shock and vibration tested
- Encapsulated module electronics
- Metal connector
- Degree of protection IP67


M12 × 1 Fieldbus




M12 × 1 Output



Connection - Outputs



M8 × 1 Power Supply



| | |
|-------------------------------|------------------------------------|
| Type | SCOB-04A-0009 |
| ID | 6824146 |
| Number of channels | 4 |
| Operating / load voltage | 20...29 VDC |
| Operating current | ≤ 40 mA |
| Fieldbus transmission rate | 10 kbps ...1 Mbps |
| Fieldbus addressing | 0 to 99 |
| Service interface | parameterisation via I/O-ASSISTANT |
| Electrical isolation | Fieldbus to operational voltage |
| Number of channels | 4 analogue outputs 20 mA |
| Load resistance | < 500 Ω |
| Electrical isolation | channels to operational voltage |
| Conversion time | < 3,5 ms |
| Relative measuring error | < +- 0.3 % of full scale |
| Actuator power supply | from load voltage |
| Dimensions (W x L x H) | 30 x 175 x 26.5 mm |
| Vibration test | Acc. to EN 60068-2-6 |
| Shock test | acc. to DIN EN 60068-2-27 |
| Electromagnetic compatibility | Acc. to EN 61000-6-2/EN 61000-6-4 |
| Protection class | IP67 |
| Approvals | CE, cULus |