


BL20 electronic module

Power Feeding Module with Diagnostics Function

BL20-PF-120/230VAC-D



- Fieldbus and connection technology independent
- Protection class IP20
- LEDs indicating system status, field supply and diagnostic information
- Can be used to form potential groups
- Supplies field with 120/230 VAC nominal voltage




Functional principle

BL20 electronic modules are plugged into the purely passive base modules which are used for connection of field devices. Maintenance is significantly facilitated due to separation of the connection level from the module electronics. Furthermore flexibility is enhanced because the base modules provide a choice of tension spring or screw connection technology.

The electronic modules are completely independent of the type of higher level field bus through the use of gateways.

Type	BL20-PF-120/230VAC-D
ID	6827008
Field supply	120 / 230 VAC
Admissible range	acc. to EN 61131-2
Nominal current from module bus	≤ 25 mA
Max. field supply current	10 A
Output connectivity	Screw, tension spring
Number of diagnostic bits	4
Dimensions (W x L x H)	12.6 x 74.1 x 55.4 mm
Approvals	CE, cULus
Ambient temperature	0...+55 °C
Storage temperature	-25...+85 °C
Relative humidity	15...95 %, no condensation allowed
Vibration test	Acc. to EN 61131
Shock test	Acc. to IEC 60068-2-27
Drop and topple	Acc. to IEC 60068-2-31
Electromagnetic compatibility	Acc. to EN 61131-2
Protection class	IP20
MTTF	1996 years acc. to SN 29500 (Ed. 99) 20 °C

Compatible base modules

Dimension drawing	Type	Pin configuration
	BL20-P3T-SBB 6827036 Tension spring connection BL20-P3S-SBB 6827037 Screw connection	Wiring Diagram 
	BL20-P4T-SBBC 6827038 Tension spring connection, access to C rail BL20-P4S-SBBC 6827039 Screw connection, access to C rail	Wiring Diagram 