


BL20 Economy Module

4 Analog Outputs for Current/Voltage

BL20-E-4AO-U/I



- Fieldbus-independent
- Electronics and connection technology in one housing
- Connectivity: Push-in terminals
- Protection class IP20
- LEDs indicate status and diagnostic
- Electronics galvanically separated from the field level via optocouplers
- 4 analog outputs
- 0 ... 20 mA, 4 ... 20 mA, -10 ... +10 VDC or 0 ... +10 VDC,
- Selectable per channel

Functional principle


Electronics and connection technology are integrated in the housing. A base module is not needed. Economy modules and modules with separate electronics and connection technology can be fitted into a station, provided the base modules feature tension spring connections.

The use of gateways makes economy modules completely independent from the higher level fieldbus.

Type	BL20-E-4AO-U/I
ID	6827328
Number of channels	4
Rated voltage from the supply terminal	24 VDC
Admissible range	18...30 VDC
Nominal current from field supply	≤ 130 mA
Nominal current from module bus	≤ 50 mA
Power dissipation, typical	≤ 2.6 W
Output connectivity	Push-in
Outputs	
Output type	0/4...20 mA or -10/0...+10 VDC
Load resistance, resistive	< 0.45 kΩ (current) or > 1 kΩ (voltage)
Load resistance, inductive	< 0.01 mH (voltage mode)
Load resistance, capacitive	< 1 μF (current mode)
Electrical isolation	electronics for the field level
Basic fault limit at 23 °C	< 0.2 %
Temperature coefficient	< 200 ppm/°C of full scale
Resolution	16 Bit
Measured-value display	16 bit signed integer
	Presentation: 16 bit signed integer
	Presentation: 12 bit left-justified
Cycle time	≤ 50 ms
Number of diagnostics bytes	4
Number of parameter bytes	12

Dimensions (W x L x H)	13 x 160.8 x 74.6 mm
Approvals	CE, Zone2, ClassI, Div.2.
Ambient temperature	0...+55 °C
Storage temperature	-25...+85 °C
Relative humidity	15...95 %, no condensation allowed
Vibration test	Acc. to EN 61131
Shock test	Acc. to IEC 60068-2-27
Drop and topple	Acc. to IEC 60068-2-31
Electromagnetic compatibility	Acc. to EN 61131-2
Protection class	IP20
MTTF	331 years acc. to SN 29500 (Ed. 99) 20 °C

Terminal assignment

	Analog Outputs	Pin Assignment <table><thead><tr><th></th><th>U</th><th>I</th></tr></thead><tbody><tr><td>1</td><td></td><td></td></tr><tr><td>2</td><td></td><td></td></tr><tr><td>3</td><td></td><td></td></tr><tr><td>4</td><td></td><td></td></tr></tbody></table> 		U	I	1			2			3			4		
	U	I															
1																	
2																	
3																	
4																	