


FCIC-G1/4A4P-LIL-H1141/1.0

Flow Monitoring – Compact Inline Flow Sensors of the FCIC Series

Analog Output 4...20 mA Linearized for Water




Features

- Thermodynamic operating principle
- flow monitoring of water
- Ready for use, no alignment
- Operating range 0.05...1.0 l/min
- Initial value 4 mA at 0 l/min
- End value 20 mA at 1 l/min
- Load resistance, 200 ... 500 Ohm
- Operating voltage side polarized
- Analog output 4...20 mA
- Linearized for water
- Compact design
- Incl. adapter

Technical data

| | |
|-------------------------|--------------------------------------|
| ID | 6870783 |
| Type | FCIC-G1/4A4P-LIL-H1141/1.0 |
| Mounting conditions | Inline sensor |
| Flow operating range | 0.05...1 l/min |
| Stand-by time | typ. 10 s (2...15 s) |
| Switch-on time | typ. 1 s (0.5...10 s) |
| Medium temperature | 0...+60 °C |
| Ambient temperature | 0...+60 °C |
| Electrical data | |
| Operating voltage U_B | 21.6...26.4 VDC |
| Current consumption | ≤ 70 mA |
| Output function | Analog output |
| Current output | 4...20 mA |
| Protection class | IP67 |
| Mechanical data | |
| Design | Inline |
| Housing material | Plastic, PBT-GF30 |
| Sensor material | Stainless steel, 1.4571 (AISI 316Ti) |
| Electrical connection | Connector, M12 × 1 |
| Pressure resistance | 10 bar |
| Process connection | G 1/4" |
| Tests/approvals | |
| Approvals | cULus |
| UL registration number | E210608 |

Wiring diagram



Functional principle

The FCIC inline flow sensors operate on the thermodynamic principle.

Depending on the version the sensors detect aqueous media from 0.05 to 2 l/min. In addition to the classic transistor switching output there is also a linear 4 ... 20 mA and a linear pulse output available with a clock rate of 1 ml/pulse.

The sensors are already pre-configured and must no longer be matched by the customer. They are therefore immediately ready for operation.




To ensure a linear signal over the entire coverage, the sensors must be operated with the supplied adapter. The sensors with analog and pulse output provide a linear signal proportional to the flow rate in the specified operating range. However, it must be noted that water additives can lead to linear deviation.

In addition, the stable and small-scale design makes the sensors resistant to moisture and vibration. It also simplifies the integration into already existing and new applications. Not least in hard-to-reach places the FCIC play to their strengths.

Mounting instructions

| | |
|-------------------|---|
| Mounting adapter | All sensors of the FCIC series are used with an adapter. This ensures a linear signal over the entire coverage. The adapter is screwed on to the process connection at the infeed side. |
| Mounting position | <p>In order to minimize potential misinterpretations due to disturbance, it is recommended to position the sensor with a minimum separation distance of 3 x di before and 5 x di after bends, changes in cross section, valves, etc..</p> <p>■ If deposits are likely to built up, it is recommended to clean the sensor at regular intervals and to select the associated service interval accordingly.</p> <p>■ If the sensor is mounted in vertical piping systems, it is recommended to position the sensor within the riser.</p> |

Accessories

| Dimension drawing | Type | ID | |
|---|---------------------|---------|---|
|  | RKC4.4T-P7X2-10/TXL | 6626184 | Connection cable, M12 female connector, straight, 4-pin, LED, cable length: 10 m, jacket material: PUR, black; cULus approval |
|  | RKC4.4T-2/TXL | 6625503 | Connection cable, M12 female connector, straight, 4-pin, cable length: 2 m, jacket material: PUR, black; cULus approval |
|  | WKC4.4T-2/TXL | 6625515 | Connection cable, M12 female connector, angled, 4-pin, cable length: 2 m, jacket material: PUR, black; cULus approval |