


# EC-FS4.5-0.5/16




## Male Receptacle with Stranded Wires, Front-mounted





Technical data

Type	EC-FS4.5-0.5/16
ID	6934617
Connector A	Male, M12 × 1, Straight, A-coded
Number of pins	5
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, PA GF, Black
Flange housing	Brass, CuZn, Nickel-plated
Mounting type	front panel mounting
Screw-in thread seal	Plastic, NBR
Screw-in thread	M16 × 1.5
Connection mode	Wire connection
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Protection class	IP67, (screwed together)
Cable length	0.5 m
Core insulation	PVC
Core cross-section	5 x 0.34 mm²
Core colors	BN, WH, BU, BK, GY
Electrical properties at +20 °C	
Rated voltage	60 V
Current	4 A
Insulation resistance	≥ 10 <sup>9</sup> Ω
forward resistance	≤ 5 mΩ
Mechanical and chemical properties	
Ambient temperature (fixed)	-30...+90 °C
Approvals	CE

Features

- 
- M12 × 1 male receptacle
  - Protection class IP67
  - Front panel mounting
  - Connected via stranded wires
  - 5-pin
  - Stranded wire length: 0.5 m

Contact assignment



Front panel mounting

