
TN840/920-Q120L130-H1147 UHF Read/Write Device






Technical data

Туре	TN840/920-Q120L130-H1147		
ID	7030536		
Electrical data			
Operating voltage	1224 VDC		
	≤ 1000 mA		
DC rated operational current			
Data transfer	Alternating electromagnetic field		
Technology	UHF RFID		
Region (UHF)	China (920.5924.5 MHz)		
Radio communication and protocol standards	ISO 18000-63 EPCglobal Gen 2		
Channel spacing	250 kHz		
Output power	≤ 0.5 W (ERP), adjustable		
Antenna polarization	RHCP		
Antenna HPBW	110°		
Output function	4-wire, Read/Write		
Mechanical data			
Mounting conditions	Non-flush		
Ambient temperature	-20+50 °C		
Design	Rectangular		
Dimensions	130 x 120 x 60 mm		
Housing material	Aluminium, AL, Silver		
Active area material	Plastic, ABS, black		
Vibration resistance	55 Hz (1 mm)		
Shock resistance	30 g (11 ms)		
Protection class	IP67		
Electrical connection	M12 × 1		
MTTF	51 years acc. to SN 29500 (Ed. 99) 40 °C		
Power-on indication	LED, Green/Yellow/Red		
Power-on indication	LED, Green/Yellow/Red		

Features

- Rectangular, height 60 mm
- ■Active face in front
- ■Plastic, ABS
- Device only suitable for operation in China (CHN) at 920...925 MHz

.../S2503 Connectors



.../S2500 Connectors



.../S2501 Connectors



Functional principle

The UHF read/write heads form a transmission zone, the size of which may vary depending on the combination of read/write head and tag used.



Technical data

Diagnostic display	differently adjustable
Packaging unit	1

The read/write distances only represent standard values measured under laboratory conditions, free from any influences caused by surrounding materials.

Attainable distances may vary due to component tolerances, mounting conditions, ambient conditions and material qualities, especially when mounted in metal.


Testing of the application under real operating conditions is therefore essential, especially with on-the-fly reading and writing!

Due to the higher energy needs of the transponder for a write operation, the range is reduced to approximately 40–60 % of the reading range.

Accessories

RH-Q240L280/Q280L640

7030296



Arm bracket for UHF RFID read/write heads TNxxx-Q175L200-H1147, TNxxx-Q240L280-H1147 and TNxxx-Q280L640-H1147

Accessories

Dimension drawing	Туре	ID	
M12x1 0 15 12 14	RK4.5T-2-RS4.5T/S2500	6699200	BL ident cable, M12 female connector, straight to M12 male connector, straight, cable length: 2 m, jacket material: PUR, yellow; other cable lengths and qualities available, see www.turck.com
M12x1 214 M12x1 015 015 015	RSCV-RKCV5500-2M/S2500	6633193	Cable for RFID applications in the food industry, M12 connector, straight to M12 female connector, straight, cable length: 2 m, jacket material: PPEDEM, white; other cable lengths and qualities available, see www.turck.com