

Handheld with Lithium-Ion Battery PD-IDENT-HF-S2D-RBTW



- Mobile reading and writing of RFID tags
- Handheld with HF antenna
- Microsoft Windows CE 5
- 2D barcode scanner (reads 1D and 2D bar codes)
- Incl. TURCK RFID software TW-HF for reading and writing of data
- Customized software solution on request
- Bluetooth
- Protection class IP65
- Withstands multiple drops on concrete from 1.5 m height
- Incl. pistol grip, docking station with power supply, USB cable
- Optionally available on request: WLAN and software development kit (SDK)

Type	PD-IDENT-HF-S2D-RBTW
ID	7030539
Ambient temperature	-20...+50 °C
Storage temperature	-40...+60 °C
Electrical data	
Data transfer	Inductive coupling
Operating frequency	13.56 MHz
Radio communication and protocol standards	ISO 15693
Device features	
Memory	XScale, 624 MHz
Display	1-GB flash ROM; 256-MB RAM
Keyboard	3.7, 640 × 480, Touchscreen
Battery capacity	55 Keys
Communication via	3300 mAh
Included software	Bluetooth Class II
Operating system	Turck RFID software, SDK available as free download
Barcode	WinCE
Docking station connection type	2D Imager (reads 1D and 2D bar codes)
	USB (serial)
Mechanical data	
Dimensions	260x 100x 42mm
Housing material	Plastic, Black
Protection class	IP65
Approvals	CE; FCC Id: GM3HFT2G2; IC Id: 2739D-HFT2G2; Safety: CSA/UL60950-1, IEC60950-1, EN60950-1; EMC: FCC Part 15 Class B EN55022; EN 55024; EN301 489

Handheld with Lithium-Ion Battery PD-IDENT-HF-S2D-RBTW

Accessories

Type code	Ident no.		Dimension drawing
PD-IDENT-TA-RS232	7030554	RS232 adapter cable for direct connection of the TA handhelds to a device with RS232-interface (e.g. PLC, PC)	
PD-IDENT-TW-3300	7030517	Replacement battery 3300 mAh	
PD-IDENT-TA-STYLUS	7030550	replacement pens (5 pcs.)	
PD-IDENT-TA-STYLUS-HOLDER-KIT	7030549	Stylus with holder (only usable without pistol grip)	
PD-IDENT-TA-POWERSUPPLY	7030597	Power supply unit	
PD-IDENT-TA-DOCK	7030596	Docking station, incl. power supply unit	