


# TP-206B-CF-H1141-L200/D805

## Temperature Detection – Probe



### Technical data

Type	TP-206B-CF-H1141-L200/D805
ID	9910521
Special version	D805 corresponds to: Pt100 for -200 °C
<b>Temperature range</b>	
Measuring range	-200...500 °C
Measuring range	-328...932 °F
Accuracy	$\pm 0.3 \text{ K} + 0.005 \cdot  t $ (-50...500 °C)
Self-heating	0.4 K/mW at 0 °C
Measuring element	Pt-100 probe, DIN EN 60751, class B, connection mode: 4-wire connection
Response time	$t_{0.5} = 6 \text{ s} / t_{0.9} = 15 \text{ s}$ in water at 0.2 m/s
Immersion depth (L)	200 mm
Outer diameter	6 mm
Protection type and class	IP67
<b>Environmental conditions</b>	
Ambient temperature	-20...+120 °C
<b>Mechanical data</b>	
Housing material	Stainless steel, 1.4404 (AISI 316L)
Sensor material	Stainless steel, 1.4404 (AISI 316L)
Process connection	For compression fittings, thermowell or direct mounting
Pressure resistance	100 bar
Electrical connection	Connector, M12 × 1
<b>Reference conditions acc. to IEC 61298-1</b>	
Temperature	15...+25 °C

### Features

- Pt 100 probe according to DIN EN 60751
- Resistant to vibrations and shocks
- Connectable to TS, TTM, IM34, BL20, BL67
- Operating temperature of the connector: -20 ... 120 °C
- 4-wire connection technology

### Functional principle

Resistance thermometers are used for the detection and monitoring of temperatures to optimize and control a process. Typical applications are in machine and plant construction as well as in the process industry. The core element of the temperature probe is a temperature-dependent resistor.


## Technical data

Atmospheric pressure	860...1060 hPa abs.
Humidity	45...75 % rel.
Auxiliary power	24 VDC
<b>Tests/approvals</b>	
Approvals	cULus
UL registration number	E345414
MTTF	2283 years acc. to SN 29500 (Ed. 99) 20 °C

## Accessories


CF-M-6-G1/4-A4 9910483

Compression fitting for direct mounting of temperature sensors; sensor diameter 6 mm; process connection G1/4" male thread




CF-M-6-N1/4-A4 9910484

Compression fitting for direct mounting of temperature sensors; sensor diameter 6 mm; process connection 1/4" NPT male thread




CF-M-6-M18-A4 9910525

Compression fitting for direct mounting of temperature sensors; sensor diameter 6 mm; process connection M18 x 1 male thread



CF-M-6-N1/2-A4 9910529

Compression fitting for direct mounting of temperature sensors; sensor diameter 6 mm; process connection 1/2" NPT male thread



CF-M-6-G1/2-A4 9910530

Compression fitting for direct mounting of temperature sensors; sensor diameter 6 mm; process connection G1/2" male thread

