


Temperature measuring amplifier

1-channel

IM12-TI02-1TCURTDR-1I1R-C0/24VDC/CC




The 1-channel temperature measuring amplifier IM12-TI02-1TCURTDR-1I1R-C0/24VDC/CC has inputs for: Thermocouples acc. to IEC 60584, DIN 43710, GOST R 8.585-2001, low voltages (-150 ... +150 mV), RTDs acc. to IEC 60751, DIN 43760, GOST 6651-94 (2, 3 and 4-wire) and resistors 0...5 kΩ (2, 3 and 4-wire).

The device is parameterized via FDT and IODD with a PC. The cold junction compensation can be set to internal, external, or to a constant value. The current output can be set to 0/4...20 mA (source or sink optional). In accordance with the parameterization, the input signals are output as a 0/4...20 mA normalized current signal. The changeover relay facilitates the monitoring of set limits for exceedance/shortfall and monitoring using a window function.

The devices have a green power LED (Pwr) and a red LED to indicate internal faults. For each input circuit there is a yellow and a red status LED. A fault in the input circuit leads to a flashing red LED according to NE44, an internal error to a steady red LED. The fault current can be adjusted to < 3.5 mA or > 21.5 mA.


The device can be used in safety circuits up to SIL2 (high and low demand according to IEC 61508) and meets the requirements of NE21. It is equipped with removable spring type terminals.

The device is equipped with removable spring-type terminals.




- Input circuits monitored for wire-break and short-circuit
- Parameterized via PC
- Complete galvanic isolation
- Removable spring type terminals
- ATEX use in Zone 2, cUL
- SIL 2

Dimensions



Output relay – Load curve



Type	IM12-TI02-1TCURTD R-111R-C0/24VDC/CC
ID	7580526

Nominal voltage	24 VDC
Operating voltage U_s	10...30 VDC
Power consumption	≤ 2 W
Power dissipation, typical	≤ 1.6 W

Input circuits	RTD Type DIN EN 60751 Pt50, Pt100, Pt 500, Pt1000
	RTD Type DIN EN 43760 Ni50, Ni100, Ni500, Ni1000
	RTD Type Gost 6651-94 Pt50, Pt100, Pt 500, Pt1000, CU50, Cu53, Cu100, CU500, CuZn100
	TC Type DIN EN 60584 Type A, Type B, Type C, Type E, Type J, Type K, Type N, Type R, Type S, Type T
	TC Type DIN 43710 Type L
	TC Type Gost 8.585-2001 Type A1, Type A2, Type A3, Type L, Type M
	Low voltage input -150...150 mV
	Resistance input 0...5000 ohms
Reference temperature	23 °C

Output circuits	
Output current	Source/sink (10...30 V) 0/4...20 mA
Load resistance current output	≤ 0.8 k Ω
Output circuits (digital)	1 x relay (change-over)
Output switching voltage relay	≤ 30 VDC / ≤ 250 VAC
Switching current per output	≤ 2 A
Switching capacity per output	≤ 500 VA/60 W
Switching frequency	≤ 15 Hz
Contact quality	AgNi




Response characteristic	
Reference temperature	23 °C
Measuring accuracy current output (including linearity, hysteresis and repeatability)	± 10 μ A
Temperature drift analog output	0.0025 %/K
Accuracy, RTD input, 0...500 ohm	± 50 m Ω
Temperature drift, RTD input, 0...500 ohm	± 5 m Ω /K
Accuracy, RTD input, 500...5000 ohm	± 500 m Ω
Temperature drift, RTD input, 500...5000 ohm	± 30 m Ω /K
Measuring accuracy TC input (including linearity, hysteresis and repeatability)	± 15 μ V
Temperature drift, TC input	± 3.2 μ V/K
Cold junction compensation error	with cold junction compensation < 2 K
Note	With a 3-wire connection, the errors double

Galvanic isolation	
Test voltage	2.5 kV RMS
Input 1 to output 1	375 V peak value acc. to EN 60079-11
Input 1 to supply	300 V RMS according to EN 50178 and EN 61010-1
A1A supply voltage	300 V RMS acc. to EN 50178 and EN 61010-1
A1D supply voltage	300 V RMS acc. to EN 50178 and EN 61010-1
A1A-A1D	300 V RMS acc. to EN 50178 and EN 61010-1

Important note	For Ex-applications the values specified in the corresponding Ex certificates (ATEX, IECEx, UL, etc.) apply.
Important note	If the device is used in applications to achieve functional safety according to IEC 61508, the safety manual must be used. Information in the data sheet are not valid for functional safety.
Use in SIL safety circuits	SIL 2 acc. to IEC 61508
Displays/Operating elements	
Operational readiness	Green
Switching state	Yellow
Error indication	red

Mechanical data		
Protection class	IP20	
Flammability class acc. to UL 94	V-0	
Ambient temperature	-25...+70 °C	
Storage temperature	-40...+80 °C	
Dimensions	120 x 12.5 x 128 mm	
Weight	167 g	
Mounting instructions	DIN rail (NS35)	
Housing material	Plastic, Polycarbonate/ABS	
Electrical connection	Removable spring-type terminals, 2-pin	
Terminal cross-section	0.2...2.5 mm² (AWG: 24...14)	
Environmental conditions	Operating height	Up to 2000 m above sea level
	Pollution degree	II
	Surge/Overvoltage category	II (EN 61010-1)
	Standards used	
	Voltage resistance and insulation	
		EN 50178
		EN 61010-1
		EN 50155
		GL VI-7-2
	Shock	
		EN 61373 class B
		EN 50155
		GL VI-7-2
		EN 60068-2-6
		EN 60068-2-27
	Temperature	
		EN 60068-2-1 Ad
		EN 50155
		GL VI-7-2
		EN 60068-2-2 Bd
		EN 60068-2-1
	Air humidity	
		EN 60068-2-38
	EMC	
		EN 50155
		GL VI-7-2
		NE21
		EN 61326-1
		EN 61326-3-1
		EN 61000-4-2
		EN 61000-4-3
		EN 61000-4-4
		EN 61000-4-5
		EN 61000-4-6
		EN 61000-4-11
		EN 61000-4-29
		EN 55011
		EN 55016
		EN 50121-3-2
		EN 61000-6-2

Accessories

Type code	Ident no.		Dimension drawing
USB-2-IOL-0002	6825482	IO-Link Master with integrated USB port	 LED-CH1 (C/Q) CH2 (DI/DO) Error USB-Mini LED-PWR IN-DC 41 54 24 16 M12 x 1
IOL-COM/3M	7525110	IO-Link communication line for connecting IO-Link devices to an IO-link master via a 3.5-mm jack plug	 ø 15 14 18.2 49.5 L 52 ø 3.5 M12 x 1
IMX12-SC-2X-4BK	7580940	Screw terminals for IM(X)12 modules; included in delivery: 4 pcs. of 2-pin black terminals	
IMX12-CC-2X-4BK	7580942	Spring terminals for IM(X)12 modules; included in delivery: 4 pcs. black terminals, 2-pin	
IMX12-2-CJT	100003646		