


Actuator and Sensor Cable
Extension Cable
RKC 4.4T-2-RSC 4.4T/S3060



- M12 female connector, straight, 4-pin
- M12 male connector, straight, 4-pin
- Instrumentation Tray Cable
- TPE jacket, yellow, 4 × 18 AWG
- UV resistant
- -40 °C cold bending strength
- Oil resistant
- Fire classes: UL 1685 FT4, UL1061, CSA FT4
- Flexlife and C-Track approved

Type	RKC 4.4T-2-RSC 4.4T/S3060
ID	U-30985
Connector A	Female, M12 × 1, Straight, A-coded
Design specification	acc. to IEC 61076-2-101
Number of pins	4
Contact carriers	Plastic, Nylon or TPU, Black
Connector body	Plastic, TPU, Yellow
Coupling nut/screw	Brass, CuZn, Nickel-plated
Seal	O ring, Plastic, FKM/FPM
Tightening torque (range)	0.8 ... 1 Nm (observe max. torque of mating connector!)
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Protection class	IP68, IP69K
	NEMA: 1, 3, 4, 6P

Connector B	Male, M12 × 1, Straight, A-coded
Design specification	acc. to IEC 61076-2-101
Number of Pins	4
Contact carriers	Plastic, TPU, Black
Connector body	Plastic, TPU, Yellow
Coupling nut/retaining screw	Brass, CuZn, Nickel-plated
Tightening torque	0.8 ... 1 Nm (observe max. torque of mating connector!)
Mechanical life	> 100 Mating cycles
Pollution degree	3
Protection class	IP68, IP69K
	NEMA: 1, 3, 4, 6P

Cable



Circuit Diagram

1	BN	- 1
2	WH	- 2
3	BU	- 3
4	BK	- 4

Cable ID	RF50956
Number of cores	4
Cable diameter	Ø 6.86mm
Cable length	2 m m
Cable jacket	TPE, Yellow
Conductor diameter	0.076 "
Conductor material	TC (tinned copper)
Core insulation	PVC
Core cross-section	4 x 18 AWG [Similar to 0.75 mm²]
Arrangement of strands	19 x 0.0092"
Core colors	BN, WH, BU, BK

Electrical properties at +20 °C

Rated voltage	250V
Current	4AA

Mechanical and chemical properties

Bending radius (stationary installation)	≥ 5 x Ø
Bending radius (flexible use)	≥ 10 x Ø
Cold flexural strength	-40 °C
Bending cycles 20 x Ø	10 million cycles
	When correctly installed at 20 °C, 50 % RH and a cycle speed of ≤ 0.5 cycles per second.
C-track	Yes
Ambient temperature (fixed)	-40...+105°C
Ambient temperature (mobile)	5...+105°C
Ambient temperature during installation	-10...+105 °C

Approval

Note

Using the cable in extreme temperatures, when it is exposed to certain chemicals and above the nominal cycle speed or below the nominal bending radius of the cable can reduce the flexural strength.

- We reserve the right to make technical modifications without prior notice.