


RSFV 49-0.25M/14.5/C1117

FOUNDATION fieldbus Flanschanschluss – Flange



Features



- 7/8" minifast Flanschstecker
- 1/2"-14 NPT screw-in thread
- Stainless steel flange housing
- 4-pin, wire length 0.25 m
- For use in FOUNDATION fieldbus applications

Headline Wiring Diagram

Pin Assignment

FOUNDATION™ fieldbus Conn



Technical data

Type	RSFV 49-0.25M/14.5/C1117
ID	U-95306
Connector A	Male, 7/8"-16 UN, Straight
Number of pins	4
Contacts	Metal, CuZn, Gold-plated
Contact carriers	Plastic, TPU, Black
Seal	Plastic, NBR
Flange housing	Stainless Steel, 1.4401 (AISI 316), Passivated
Mounting type	front panel mounting
Screw-in thread	1/2"-14 NPT
Connection mode	Wire connection
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Protection class	IP67, (screwed together)
Network protocol	FOUNDATION fieldbus
Cable length	0.25 m, (tolerance: +10 mm)
Core insulation	PVC
Core cross-section	4 x 0.8 mm ²
Core colors	BU, BN, GY, GNYE
Electrical properties at +20 °C	
Rated voltage	600 V
Current	9 A
Insulation resistance	≥ 10 ⁸ Ω
forward resistance	≤ 5 mΩ
Mechanical and chemical properties	
Ambient temperature (fixed)	-40...+105 °C

Technical data

Ambient temperature (mobile)	-40...+105 °C
Approvals	CE RoHS
Note	- We reserve the right to make technical modifications without prior notice.