



IP-Link için piconet Uzatma Modülü 1-channel SSI Sensor Interface SNNE-10S-0005




- SSI encoder interface
- 1-channel
- Parameterizable functions
- Supported via I/O-ASSISTANT 2
- Direct connection to the IP link
- Fibre-glass reinforced housing
- Encapsulated module electronics
- Metal connector
- Degree of protection IP67

Enkoder - M23 × 1



M8 × 1 Güç Besleme



Tip	SNNE-10S-0005
Tanıt. no.	6824214
Operating / load voltage	20...29 VDC
Operating current	≤ 55 mA
Fibre-optic length	≤ 15 m
Bit transfer	Diferansiyel (RS485)
Transmission rate	variable up to 1 MHz (default 250 Hz)
Serial input	24 bit
Data direction	read
Sensör besleme	24 VDC from load voltage
Potential separation	operating voltage to RS232
Boyutlar (W x L x H)	30 x 126 x 26.5 mm
Titreşim testi	EN 60068-2-6 uyarınca
Darbe testi	acc. to DIN EN 60068-2-27
Elektromanyetik uyumluluk	EN 61000-6-2/EN 61000-6-4 uyarınca
IP Derecesi	IP67
Onaylar	CE, cULus

Data in process image

Pre-conditions	Address	Input data		Output data	
Compact mapping: Starting with D3 in "Low-Byte" word 0 all other bytes follow immediately (highlighted in grey). Complex mapping: Data are mapped with control and status byte	Word	High-Byte	Low-Byte	High-Byte	Low-Byte
	0	D3	SB	Reg1	CB
	1	D1	D2	reserved	Reg0
	2	reserved	D0	reserved	reserved