



**Switching power supply
IM82-24-10**



The IM82-24-10 power supply unit is designed for DC consumers, in particular for the supply of switching and monitoring devices of the TURCK IM, IME, IMS and IMC series.

The power supply provides 24 VDC output voltage and 10 A output current. With the potentiometer V_{out} the output voltage can be adjusted in a range between 22.5...28.5 VDC. The device provides safety extra-low voltage (SELV) according to EN 60950.

The power supply can be set to single or parallel operating mode.




- cULus listed
- Safety extra-low voltage SELV IEC/ EN 60950
- SEMI-F47
- Output voltage adjustable 22.5...28.5 VDC
- Nominal current 10 A
- Single/parallel operating mode
- Surge protection
- Universal operating voltage
- Mains failure bridging up to 30 ms
- High efficiency
- Natural air cooling
- Power-good relay


**Switching power supply
IM82-24-10**

Type designation	IM82-24-10
Ident-No.	7545043
Ident-No (TUSA)	M7545043
Nominal voltage	Universal voltage supply unit
Operating voltage	90...132 VAC and 186...264 VAC
Frequency	47...73 Hz
Operating voltage range	210...370 VDC
Power consumption	≤ 276 VA
PFC	0.7
Efficiency	89 %
External fuse	B10A, C6A
Internal fuse	T 6.3 A / 250 VAC
Inrush current	U _i = 115 VAC, 30 A; U _i = 230 VAC, 60 A
Mains buffering	U _i = 115 VAC, 25 ms; U _i = 230 VAC, 30 ms
Nominal output voltage	24 V
Adjustment range	22.5...28.5 V
Nominal current	10 A
Output circuits (digital)	relay (NO), > 17.6 ... 19.4V
Output switching voltage relay	≤ 60 VDC / ≤ 250 VAC
Switching current per output	≤ 0.3 A
Overload protection	110-150 %
Surge limiting	120-145 %
Parallel mode	yes, switchover initiated by a switch, max. 3 devices each with 90 % load current
Ripple	100 mV
Pollution degree	2
Surge category	II
Short-circuit behaviour	Current limiting
Limit frequency	≤ 40000 Hz
Galvanic isolation	
Test voltage	3.0 kV
Indication	
Operational readiness	green
Error indication	red
Protection class	IP20
Flammability class acc. to UL 94	V-0
Ambient temperature	-25...+70 °C
Storage temperature	-25...+85 °C
Derating	-2.5%/°C from 60°C
Relative humidity	≤ 95 %
Dimensions	124.5 x 83.5 x 116.6 mm
Weight	1448 g
Mounting instructions	DIN rail (NS35)
Housing material	Metal
Electrical connection	Screw terminals
Terminal cross-section	0.2...2.0 mm ²
Tightening torque	0.5 Nm


Dimensions



Derating



Short-circuit behaviour



Parallel operation

